

Metal PlugTrak® Series

Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions

Tamper-Resistant
 USB



	Amp Circuits	Single Recept.	USB Recept.	Recept. Spacing		Ivory	Gray	Description	Color	Catalog No.
				(in)	(in)					
3 Foot	15 Single	6	-	6		HBL20GB306IV	HBL20GB306GY	1-Gang Device Box 	Ivory	HBL2048IV
									Gray	HBL2048GY
	15 IG/Single	6	-	6		HBL20IG306IV	HBL20IG306GY	2-Gang Device Box 	Ivory	HBL20482IV
									Gray	HBL20482GY
	15 TR/Single	6	-	6		HBL20GB306IVTR	HBL20GB306GYTR	External Elbow 	Ivory	HBL2018BRIV
									Gray	HBL2018BRGY
20 Single	6	-	6		HBL24GB306IV	HBL24GB306GY	Flat Elbow 	Ivory	HBL2011BRIV	
								Gray	HBL2011BRGY	
20 TR/Single	6	-	6		HBL24GB306IVTR	HBL24GB306GYTR	Tee 	Ivory	HBL2015BRIV	
								Gray	HBL2015BRGY	
5 Foot	15 Single	10	-	6		HBL20GB506IV	HBL20GB506GY	Entrance End Fitting 	Ivory	HBL2010A2IV
									Gray	HBL2010A2GY
	15 Single	5	-	12		HBL20GB512IV	HBL20GB512GY	Large Entrance End Fitting 	Ivory	HBL2010A3IV
									Gray	HBL2010A3GY
	15 Two	5	-	12		HBL20GBA512IV	HBL20GBA512GY	Blank End Fitting 	Ivory	HBL2010BIV
									Gray	HBL2010BGY
	15 IG/Single	5	-	12		HBL20IG512IV	HBL20IG512GY	Cover Clip 	Ivory	HBL2006IV
									Gray	HBL2006GY
	20 Single	10	-	6		HBL24GB506IV	HBL24GB506GY	Supporting Clip 	Galvanized Steel	HBL2003SC*
20 Single	5	-	12		HBL24GB512IV	HBL24GB512GY	Coupling 	Galvanized Steel	HBL2001C	
20 Two	5	-	12		HBL24GBA512IV	HBL24GBA512GY	Internal Corner Coupling 	Galvanized Steel	HBL2017TC	
20 TR/Single	5	-	12		HBL24GB512IVTR	HBL24GB512GYTR				
6 Foot	15 Single	12	-	6		HBL20GB606IV	HBL20GB606GY	Entrance End Fitting 	Ivory	HBL2010A2IV
									Gray	HBL2010A2GY
	15 Single	8	-	9		HBL20GB609IV	HBL20GB609GY	Large Entrance End Fitting 	Ivory	HBL2010A3IV
									Gray	HBL2010A3GY
	15 Single	6	-	12		HBL20GB612IV	HBL20GB612GY	Blank End Fitting 	Ivory	HBL2010BIV
									Gray	HBL2010BGY
	15 Single	4	-	18		HBL20GB618IV	HBL20GB618GY	Cover Clip 	Ivory	HBL2006IV
									Gray	HBL2006GY
	15 Two	8	-	9		HBL20GBA609IV	HBL20GBA609GY	Supporting Clip 	Galvanized Steel	HBL2003SC*
15 Two	6	-	12		HBL20GBA612IV	HBL20GBA612GY	Coupling 	Galvanized Steel	HBL2001C	
15 Two	4	-	18		HBL20GBA618IV	HBL20GBA618GY	Internal Corner Coupling 	Galvanized Steel	HBL2017TC	
15 IG/Single	12	-	6		HBL20IG606IV	HBL20IG606GY				
15 USB/Single4	4	4	12		HBL20GB612UIV	-				
20 Single	12	-	6		HBL24GB606IV	HBL24GB606GY				
20 Single	6	-	12		HBL24GB612IV	HBL24GB612GY				
20 Single	4	-	18		HBL24GB618IV	HBL24GB618GY				
20 Two	6	-	12		HBL24GBA612IV	HBL24GBA612GY				
20 Two	4	-	18		HBL24GBA618IV	HBL24GBA618GY				



Portable	Amp Circuits	Single Recept.	Cord Length		USB Recept. Ports	Ivory	Gray
			(in)	(ft)			
15 Single	40	6	6	-	HBL20C215IV	HBL20C215GY	
15 USB/Single	40	6	4	2	HBL20C215UIV	-	
15 Single	64	6	10	-	HBL20C315IV	HBL20C315GY	

Note: IG = Isolated Ground; TR = Tamper-Resistant; U = USB
 Hubbell Metal PlugTrak is supplied with (2) HBL2010BIV/GY blank end fittings and (1) HBL2001C coupling; Catalog No. suffix "IV" for Ivory finish and "GY" for Gray finish; outlets match raceway color; IG Isolated Ground receptacles have Orange triangles; Portable PlugTrak includes 15A circuit breaker

Note: *Support clip HBL2003SC for supporting Portable Metal PlugTrak only
 See pages U11-U12 for additional information

Delivery Raceway - Section U