

## Aluminum PlugTrak® Series

Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions

Tamper-Resistant

USB



|        | Amp Circuits |            | Single Recept. | USB Ports | Receptacle Spacing (in) | Catalog No.     |
|--------|--------------|------------|----------------|-----------|-------------------------|-----------------|
|        | 3 Foot       | 15         | Single         | 6         | -                       | 6               |
| 15     |              | IG/Single  | 6              | -         | 6                       | HBLALU20IG306   |
| 15     |              | TR/Single  | 6              | -         | 6                       | HBLALU20GB306TR |
| 15     |              | USB/Single | 2              | 2         | 12                      | HBLALU20GB312U  |
| 20     |              | Single     | 6              | -         | 6                       | HBLALU24GB306   |
| 20     |              | IG/Single  | 6              | -         | 6                       | HBLALU24IG306   |
| 20     |              | TR/Single  | 6              | -         | 6                       | HBLALU24GB306TR |
| 5 Foot | 15           | Single     | 10             | -         | 6                       | HBLALU20GB506   |
|        | 15           | Single     | 5              | -         | 12                      | HBLALU20GB512   |
|        | 15           | IG/Single  | 10             | -         | 6                       | HBLALU20IG506   |
|        | 15           | TR/Single  | 5              | -         | 12                      | HBLALU20GB512TR |
|        | 20           | Single     | 10             | -         | 6                       | HBLALU24GB506   |
|        | 20           | Single     | 5              | -         | 12                      | HBLALU24GB512   |
|        | 20           | IG/Single  | 10             | -         | 6                       | HBLALU24IG506   |
| 20     | TR/Single    | 5          | -              | 12        | HBLALU24GB512TR         |                 |
| 6 Foot | 15           | Single     | 12             | -         | 6                       | HBLALU20GB606   |
|        | 15           | Single     | 6              | -         | 12                      | HBLALU20GB612   |
|        | 15           | Single     | 4              | -         | 18                      | HBLALU20GB618   |
|        | 15           | Two        | 12             | -         | 6                       | HBLALU20GBA606  |
|        | 15           | Two        | 6              | -         | 12                      | HBLALU20GBA612  |
|        | 15           | Two        | 4              | -         | 18                      | HBLALU20GBA618  |
|        | 15           | IG/Single  | 12             | -         | 6                       | HBLALU20IG606   |
|        | 15           | USB/Single | 4              | 4         | 12                      | HBLALU20GB612U  |
|        | 20           | Single     | 12             | -         | 6                       | HBLALU24GB606   |
|        | 20           | Single     | 6              | -         | 12                      | HBLALU24GB612   |
|        | 20           | Single     | 4              | -         | 18                      | HBLALU24GB618   |
|        | 20           | Two        | 12             | -         | 6                       | HBLALU24GBA606  |
|        | 20           | Two        | 6              | -         | 12                      | HBLALU24GBA612  |
| 20     | Two          | 4          | -              | 18        | HBLALU24GBA618          |                 |
| 20     | IG/Single    | 12         | -              | 6         | HBLALU24IG606           |                 |

Note: IG = Isolated Ground; TR = Tamper-Resistant; U = USB Hubbell Aluminum PlugTrak is supplied with (2) HBLALU2010B blank end fittings and (1) HBLALU2001 coupling.

|              | Description                | Catalog No.    |            |
|--------------|----------------------------|----------------|------------|
| Device Boxes | Standard 1-Gang Device Box | HBLALU2047     |            |
|              | Deep 1-Gang Device Box     | HBLALU2044     |            |
|              | Standard 2-Gang Device Box | HBLALU20472    |            |
|              | Deep 2-Gang Device Box     | HBLALU20442    |            |
|              | Round Box                  | HBLALU2038     |            |
|              | Elbows and Tees            | External Elbow | HBLALU2018 |
|              |                            | Internal Elbow | HBLALU2017 |
| Flat Elbow   |                            | HBLALU2011     |            |
| Tee          |                            | HBLALU2015     |            |
| Fittings     |                            | Cover Clip     | HBLALU2006 |
|              | Supporting Clip            | HBLALU2003     |            |
|              | Coupling                   | HBLALU2001     |            |
|              | Entrance End Fitting       | HBLALU2010A    |            |
|              | In-Line Switch Fitting     | HBLALU2040A    |            |
|              | Blank End Fitting          | HBLALU2010B    |            |

Note: See pages U35-U36 for additional information.