

HBL500, HBL700 and HBL750 Series Inches (mm)

HBL500, HBL700 and HBL750 Series	Description	Color	Length	HBL500 Series	HBL700 Series	HBL750 Series
	Base and Cover Available in 5ft (1.5m) lengths, packed 50ft (15m) per carton and 10ft (3m) lengths, packed 100ft (30m) per carton. HBL5701C coupling furnished with each length.	Ivory Ivory White	5ft 10ft 10ft	– HBL50010IV HBL50010W A: .53" (13.46) B: .76" (19.30)	– HBL700IV HBL700W A: .67" (16.90) B: .76" (19.30)	HBL7505IV HBL75010IV HBL75010W A: .85" (21.59) B: .76" (19.30)



	Color	1-Gang	2-Gang	3-Gang	4-Gang	5-Gang	6-Gang
Standard	Ivory	HBL5748IVA	HBL57482IVA	HBL57483IVA	HBL57484IVA	HBL57485IVA	HBL57486IVA
	White	HBL5748WA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	HBL57482WA A: 4.54" (115.32) B: 4.64" (117.86) C: 1.75" (44.45)	HBL57483WA A: 4.54" (115.32) B: 6.45" (163.88) C: 1.75" (44.45)	– A: 4.54" (115.32) B: 8.26" (209.91) C: 1.75" (44.45)	– A: 4.54" (115.32) B: 10.01" (255.93) C: 1.75" (44.45)	– A: 4.54" (115.32) B: 11.89" (301.96) C: 1.75" (44.45)
Shallow	Ivory	HBL5747IVA	HBL57472IVA	HBL57473IVA	–	–	–
	White	HBL5747WA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.38" (35.05)	HBL57472WA A: 4.54" (115.32) B: 4.64" (117.86) C: 1.38" (35.05)	– A: 4.54" (115.32) B: 6.45" (163.88) C: 1.38" (35.05)	–	–	–
Deep	Ivory	HBL5744SIVA	HBL5744S2IVA	HBL5744S3IVA	–	–	–
	White	HBL5744SWA A: 4.54" (115.32) B: 2.82" (71.63) C: 2.25" (57.00)	HBL5744S2WA A: 4.54" (115.32) B: 4.64" (117.86) C: 2.25" (57.00)	– A: 4.54" (115.32) B: 6.45" (163.88) C: 2.25" (57.00)	–	–	–
Extra Deep	Ivory	HBL5744IVA	HBL57442IVA	HBL57443IVA	–	–	–
	White	HBL5744WA A: 4.54" (115.32) B: 2.82" (71.63) C: 2.75" (69.85)	HBL57442WA A: 4.54" (115.32) B: 4.64" (117.86) C: 2.75" (69.85)	– A: 4.54" (115.32) B: 6.45" (163.88) C: 2.75" (69.85)	–	–	–
Base Trade Size KOs		2 - 1/2"	1 - 1/2", 3/4" Concentric 1 - Rectangular	3 - 1/2"	4 - 1/2"	5 - 1/2"	6 - 1/2"

Note: For datacom applications, box selection is dependent on depth of jacks; see Section B



Extension Boxes	Description	Color	1-Gang	1-Gang Deep	1-Gang Blank	2-Gang	3-Gang
	Extension Boxes To extend existing flush switch and receptacle boxes. Blank is used where it is desired to blank original outlet.	Ivory White	HBL5751IVA HBL5751WA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.38" (35.05)	HBL5751AIVA HBL5751AWA A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	HBL5760IVA – A: 4.54" (115.32) B: 2.82" (71.63) C: 1.13" (28.70)	HBL57512IVA – A: 4.54" (115.32) B: 4.64" (117.86) C: 1.38" (35.05)	HBL57513IVA – A: 4.54" (115.32) B: 6.45" (163.88) C: 1.38" (35.05)