

# 60" Insigna

009 Brushed Nickel 163 Vintage Brass

**P250107-009-30** Brushed Nickel  
60" dia., 14.75" ht.  
*Shown with Matte Black blades  
and light kit replaced by blank plate*

Matte Black



**P250107-163-30** Vintage Brass  
60" dia., 14.75" ht.  
*Shown with Matte Black blades*

Matte Black



**P250112-163-30** Vintage Brass  
60" dia., 14.75" ht.  
*Shown with Matte White blades*

Matte White



## ENERGY INFORMATION

**Airflow** 6766 cubic feet per minute  
**Electricity Use** 35.12 watts (excludes lights)  
**DOE Weighted CFM/W** 211 CFM/W



Full Function Remote Control Included  
*Six-speed fan operation  
Full-range dimming for light  
Reverse direction control*

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20degree)
- DC Motor
- Damp Rated
- Remote control with batteries included
- ABS Blades
- Light Blank Plate Included



## LAMPING

20w LED module, 3000K, 90CRI,  
1865 source lumens, dimmable.

All fixtures:



Search the product number on [progresslighting.com](https://www.progresslighting.com) for full product details

Featuring 60" Insigna

