

72" Insigna

009 Brushed Nickel

163 Vintage Brass

P250108-009-30 Brushed Nickel

72" dia., 14.75" ht.

Shown with Matte Black blades



Matte Black



P250108-163-30 Vintage Brass

72" dia., 14.75" ht.

Shown with Matte Black blades



Matte Black



P250113-163-30 Vintage Brass

72" dia., 14.75" ht.

Shown with Matte White blades
and light kit replaced by blank plate



Matte White



ENERGY INFORMATION

Airflow	8807 cubic feet per minute
Electricity Use	28.95 watts (excludes lights)
DOE Weighted CFM/W	334 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20degree)
- DC Motor
- Damp Rated
- Remote control with batteries included
- ABS Blades
- Light Blank Plate Included



LAMPING

20w LED module, 3000K, 90CRI,
1865 source lumens, dimmable.

All fixtures:

