

Belen

009 Brushed Nickel 31M Matte Black

P250111-009-30 Brushed Nickel
60" dia., 13.56" ht.
Shown with Matte Black blades

Matte Black



P250117-009-30 Brushed Nickel
60" dia., 13.56" ht.
Shown with Silver blades

Silver



P250117-31M-30 Matte Black
60" dia., 13.56" ht.
Shown with Matte Black blades

Matte Black



ENERGY INFORMATION

Airflow 6469 cubic feet per minute
Electricity Use 35 watts (excludes lights)
DOE Weighted CFM/W 206 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20degree)
- DC Motor
- Damp Rated
- Remote control with batteries included
- PC Blades

LAMPING

20w LED module, 3000K, 90CRI,
1865 source lumens, dimmable.

All fixtures:



Search the product number on [progresslighting.com](https://www.progresslighting.com) for full product details

Featuring Belen

