

# Bexar

009 Brushed Nickel

31M Matte Black

## P250099-009-30 Brushed Nickel

54" dia., 11.5" ht.

Shown with Dark Cherry blades



Silver



Dark Cherry



## P250099-31M-30 Matte Black

54" dia., 11.5" ht.

Shown with Distressed Ebony blades



Distressed Ebony



Matte Black



### ENERGY INFORMATION

<b>Airflow</b>	3,576 cubic feet per minute
<b>Electricity Use</b>	64 Watts (excludes lights)
<b>DOE Weighted CFM/W</b>	64 CFM/W



Three-speed Remote Control Included  
Three-speed fan operation

### FEATURES

- Limited Lifetime Warranty
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries included
- Add the P2667-31 WiFi remote control

### LAMPING

18w LED Module, 3000K, 90 CRI,  
1600 source lumens, dimmable.

All fixtures:

