

# Brazas

009 Brushed Nickel 31M Matte Black

Fashionably detailed with bracketed trim, the Brazas 56-inch ceiling fan features six ABS fan blades and a quiet and energy-efficient DC motor to keep spaces cool in style. This fan is light kit adaptable and includes a full-function remote control with a wall bracket. Available in matte black with distressed ebony blades and brushed nickel with grey weathered wood blades and a UL damp rating, Brazas fits beautifully into transitional indoor or outdoor settings.



P250100-31M

# Brazas

**P250100-009** Brushed Nickel  
56" dia., 13" ht.  
*Shown with Gray Weathered Wood blades*

Grey Weathered Wood



**P250100-31M** Matte Black  
56" dia., 13" ht.  
*Shown with Distressed Ebony blades*

Distressed Ebony



## ENERGY INFORMATION

<b>Airflow</b>	6,621 cubic feet per minute
<b>Electricity Use</b>	31 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	245 CFM/W



Full Function Remote Control Included  
*Six-speed fan operation*  
*Full-range dimming for light*  
*Reverse direction control*

## FEATURES

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- Damp Rated
- Remote control with batteries included

All fixtures:

