

Burnett

009 Brushed Nickel

31M Matte Black

P250116-009-30 Brushed Nickel

21" dia., 9.75" ht.

Shown with Chrome accent



Chrome



P250116-31M-30 Matte Black

21" dia., 9.75" ht.

Shown with Vintage Brass accent



Vintage Brass



ENERGY INFORMATION*

Airflow N/A

Electricity Use N/A

DOE Weighted CFM/W N/A

*Data not available at time of printing



Full Function Remote Control Included

Six-speed fan operation

Full-range dimming for light

Reverse direction control

FEATURES

- 360° Oscillation
- Limited Lifetime Warranty
- Close to Ceiling Mount
- DC Motor
- Damp Rated
- Remote Control with Batteries Included
- Edge lit LEDs
- Rust Proof Blades

LAMPING

32W LED Strip, 3000K, 90 CRI,
1900 Source Lumens, Dimmable

All fixtures:

