

Nealy

FINISH

● Brushed Nickel - 009

ALSO IN

Bath

PAIR WITH

Lassiter
Clarion

P400141-009



Silk Shades

Curving Details

Mixed Metals

Nealy offers classic charm with an edge of modern luxury. Curving details and candelabra arms are complemented by luxurious off-white silk shades. Featuring mixed metal influences, the Brushed Nickel frame is accentuated with Graphite detailing and completed with clear and brass-tone accents.



P400142-009



P400141-009
*shown
without
shades*



P400150-009



P500141-009



P710046-009

Nealy

FIVE-LIGHT CHANDELIER

P400141-009 Brushed Nickel
28-3/8" dia., 28-1/4" ht.,
Overall ht. w/chain 102-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400142-009 Brushed Nickel
36" dia., 37-1/2" ht.,
Overall ht. w/chain 159-1/2"; wire 15'.
Nine candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER

P400150-009 Brushed Nickel
21-1/2" dia., 21-3/8" ht.,
Overall ht. w/chain 96-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

MINI-PENDANT

P500141-009 Brushed Nickel
7-1/4" dia., 16-3/4" ht.,
Overall ht. w/stem 80"; wire 10'.
One medium base lamp,
100w max.

WALL BRACKET

P710046-009 Brushed Nickel
5-1/2" dia., 16-5/8" ht.,
Extends 7". H/CTR 7-1/2".
One candelabra base lamp,
60w max.

Nealy

FINISH

● Brushed Nickel - 009

ALSO IN

Collections

P300142-009

Nealy offers classic charm with an edge of modern luxury. Curving details and candelabra arms are complemented by luxurious white glass shades. Featuring mixed metal influences, the Brushed Nickel frame is accentuated with Graphite detailing and completed with clear and brass-tone accents.

Classic Charm



Mixed Metals

White Glass Shades

TWO-LIGHT BATH

P300141-009 Brushed Nickel
13-1/2" W., 9" ht.
Extends 6". H/CTR 6-3/8".
Two medium base lamps,
each 100w max.



P710046-009

THREE-LIGHT BATH

P300142-009 Brushed Nickel
23" W., 9" ht.
Extends 6". H/CTR 6-3/8".
Three medium base lamps,
each 100w max.



P300143-009

FOUR-LIGHT BATH

P300143-009 Brushed Nickel
30" W., 9" ht.
Extends 6". H/CTR 6-3/8".
Four medium base lamps,
each 100w max.



P300141-009

WALL BRACKET

P710046-009 Brushed Nickel
Off-white silk shade.
5-1/2" W., 16-5/8" ht.
Extends 7". H/CTR 7-1/2".
One candelabra base lamp,
60w max.



P300142-009

*All fixtures mount up or down,
except P710046-009.*

Nealy

Curved mixed metal, shimmering glass, and silk shade combine for classic charm and modern luxury.

P710046-009 Brushed Nickel
5-1/2" dia., 16-5/8" ht.
Extends 7". H/CTR 7-1/2".
One candelabra base lamp,
60w max.



P710046-009