

Rainey

FINISHES

- Brushed Nickel - 009
- Graphite - 143

PAIR WITH

- Landree
- Blakely

P400167-009



Ribbed Glass Shades

Rainey embraces an artful display of asymmetrical design styling. A slender, staggered frame representing organic forms draws the eye upward to admire the fluted ribbed glass shades. The larger scale is suitable for open floor plans, great rooms or anywhere a dramatic focal piece is needed to make a bold statement. Rainey is available in Graphite with Brushed Bronze accents or Brushed Nickel.

Asymmetrical Design

Organic Form



P400168-009



P350122-009

SEMI-FLUSH CONVERTIBLE

P350122-009 Brushed Nickel
Hanging and ceiling mount hardware included.
18" dia., 16" ht.,
Overall ht. w/stem 81-1/2"; wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400167-009 Brushed Nickel
24" dia., 22-1/4" ht.,
Overall ht. w/stem 88-1/2"; wire 15'.
Five candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER

P400168-009 Brushed Nickel
28" dia., 25-1/4" ht.,
Overall ht. w/stem 91-1/2"; wire 15'.
Six candelabra base lamps, each 60w max.

WALL BRACKET

P710056-009 Brushed Nickel
11-1/2" W., 16-1/2" ht.,
Extends 5-1/8" H/CTR 5-5/8".
Two candelabra base lamps, each 60w max.



P350122-009
shown as semi-flush



P400167-009



P710056-009

All fixtures shown with EF4T8D927/JA8 LED lamps, not included.



Mix Modern & Natural Styles

Modern and rustic have never looked so good together. Take a cue from the artful placement of the asymmetrically designed Rainey chandelier over the organic shape of a rough-hewn table-top and bench. Use a neutral color palette on the cabinets and walls to lend a sleek look, but be sure to add details such as pairing textured fabric on the otherwise modern style of the dining chairs to keep the look from becoming cold. Finish with undercabinet lighting to cast the perfect amount of light on countertop tasks.

Rainey



P400168-143



P350122-143

SEMI-FLUSH CONVERTIBLE

P350122-143 Graphite
Hanging and ceiling mount hardware included.
18" dia., 16" ht.,
Overall ht. w/stem 81-1/2"; wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400167-143 Graphite
24" dia., 22-1/4" ht.,
Overall ht. w/stem 88-1/2"; wire 15'.
Five candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER

P400168-143 Graphite
28" dia., 25-1/4" ht.,
Overall ht. w/stem 91-1/2"; wire 15'.
Six candelabra base lamps, each 60w max.

WALL BRACKET

P710056-143 Graphite
11-1/2" W., 16-1/2" ht.,
Extends 5-1/8" H./CTR 5-5/8".
Two candelabra base lamps, each 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included.



P400167-143



P350122-143
shown as semi-flush



P710056-143

Rainey

Asymmetrical styling, mixed metal and clear fluted ribbon glass make a bold statement.

P710056-009 Brushed Nickel

P710056-143 Graphite

11-1/2" W., 16-1/2" ht.

Extends 5-1/8". H/CTR 5-5/8".

Two candelabra base lamps, each 60w max.

Fixture shown with P7826-01 vintage lamp.



P710056-143



P710056-009