

Bowman

FINISHES

- Matte Black - 031
- Cottage White - 151

ALSO IN

- Bath
- Close-to-Ceiling

PAIR WITH

- Whisp
- Bonn

P400194-031

The Bowman Collection, with its slightly larger scale and gracefully sweeping arms appeal to both classic taste and artistic spirit. Clear chiseled shades adorn elegant light bases topped with traditional candle slips, offering the ultimate refined look.



Elegant Design

Clear Chiseled Glass

Sweeping Arms



P400196-031



P400195-031



P500207-031



P400194-031



P350148-031

Bowman

SEMI-FLUSH CONVERTIBLE

P350148-031 Matte Black
Hanging and ceiling mount hardware included.
14-1/4" dia., 13-3/8" ht.,
Overall ht. w/chain 52-1/2", wire 10'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400194-031 Matte Black
26" dia., 23-1/4" ht.,
Overall ht. w/chain 98-1/4", wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400195-031 Matte Black
32" dia., 28-7/8" ht.,
Overall ht. w/chain 104", wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400196-031 Matte Black
37" dia., 33-1/4" ht.,
Overall ht. w/chain 156-1/4", wire 15'.
Nine candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500207-031 Matte Black
14-1/4" dia., 26-1/4" ht.,
Overall ht. w/chain 100-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

*All fixtures shown with
F4B10LED927/JA8 lamps, not included.*

Bowman

P400194-151



Beautiful and Airy

Clear Chiseled Glass

Cottage White

P400196-1511



P400195-151



P500207-151



P400194-151



P350148-151



SEMI-FLUSH CONVERTIBLE

P350148-051 Cottage White
Hanging and ceiling mount hardware included.
14-1/4" dia., 13-3/8" ht.,
Overall ht. w/chain 52-1/2", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400194-151 Cottage White
26" dia., 23-1/4" ht.,
Overall ht. w/chain 98-1/4", wire 15'.
Five candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER

P400195-151 Cottage White
32" dia., 28-7/8" ht.,
Overall ht. w/chain 104", wire 15'.
Six candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400196-151 Cottage White
37" dia., 33-1/4" ht.,
Overall ht. w/chain 156-1/4", wire 15'.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER

P500207-151 Cottage White
14-1/4" dia., 26-1/4" ht.,
Overall ht. w/chain 100-1/2", wire 15'.
Four candelabra base lamps, each 60w max.

All fixtures shown with F4B10LED927/JA8 lamps, not included.

Bowman

FINISHES

- Black - 031
- Cottage White - 151

ALSO IN

- Collections
- Close-to-Ceiling

P300254-031

Beautiful lighting will appeal to both your classic taste and your artistic spirit with the Bowman Collection. Wandering eyes will focus on clear, chiseled glass shades as they offer an air of refinery. Handsome light bases with dainty, sophisticated curved arms support elegant light bases.

Elegant Design



Sweeping Arms

Clear Chiseled Glass Shades

ONE-LIGHT BATH

P300253-031 Black
5" W., 10-3/8" ht.
Extends 7". H/CTR 3-1/2".
One medium base lamp,
60w max.



P300253-031

TWO-LIGHT BATH

P300254-031 Black
16-3/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Two medium base lamps,
each 60w max.



P300254-031

THREE-LIGHT BATH

P300255-031 Black
25" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Three medium base lamps,
each 60w max.



P300255-031

FOUR-LIGHT BATH

P300256-031 Black
33-5/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Four medium base lamps,
each 60w max.



P300256-031

All fixtures mount up or down.

Bowman

ONE-LIGHT BATH

P300253-151 Cottage White
5" W., 10-3/8" ht.
Extends 7". H/CTR 3-1/2".
One medium base lamp,
60w max.



P300253-151

TWO-LIGHT BATH

P300254-151 Cottage White
16-3/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Two medium base lamps,
each 60w max.



P300254-151

THREE-LIGHT BATH

P300255-151 Cottage White
25" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Three medium base lamps,
each 60w max.



P300255-151

FOUR-LIGHT BATH

P300256-151 Cottage White
33-5/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Four medium base lamps,
each 60w max.



P300256-151

All fixtures mount up or down.

Bowman

Clear, chiseled glass shades surround dainty yet sophisticated curved-arm candle slips.

SEMI-FLUSH CONVERTIBLE

P350148-031 Matte Black

P350148-151 Cottage White
Hanging and ceiling mount hardware included.

14-1/4" dia., 13-3/8" ht.,

Overall ht. w/chain 52-1/2", wire 10'.

Three candelabra base lamps, each 60w max.



P350148-151



P350148-031