

Durrell

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

- Bath
- Close-to-Ceiling

PAIR WITH

- Calhoun
- Hemsworth

P400199-009



The versatile Durrell Collection will find a home in any coastal, modern farmhouse, or vintage setting in need of gorgeous generous illumination. Featuring a variety of versatile materials including a sailcloth linen shade and wooden accents. Durrell will showcase a lighting experience that is welcoming and sophisticated.

Sophisticated

Curved Arms

Brushed Nickel



P400200-009



P500210-009

Durrell

SEMI-FLUSH CONVERTIBLE
P350150-009 Brushed Nickel
 Hanging and ceiling mount hardware included
 16" dia., 13-1/2" ht.,
 Overall ht. w/chain 47", wire 10'.
 Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400199-009 Brushed Nickel
 26-1/2" dia., 22-1/2" ht.,
 Overall ht. w/chain 97-1/2", wire 15'.
 Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400200-009 Brushed Nickel
 32" dia., 24-1/2" ht.,
 Overall ht. w/chain 99-1/2", wire 15'.
 Nine candelabra base lamps, each 60w max.

FOUR-LIGHT CHANDELIER
P400218-009 Brushed Nickel
 21" dia., 22-1/2" ht.,
 Overall ht. w/chain 97-1/2", wire 15'.
 Four candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500210-009 Brushed Nickel
 18" dia., 28-1/2" ht.,
 Overall ht. w/chain 103-1/2", wire 15'.
 Four candelabra base lamps, each 60w max.

WALL BRACKET
P710074-009 Brushed Nickel
 4-1/2" W., 12" ht.,
 Extends 5". H/CTR 6".
 One candelabra base lamp, 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included.



P400199-009



P400218-009



P350150-009
 shown hanging



P350150-009
 shown as ceiling mount



P710074-009