

# Durrell

## FINISHES

- Brushed Nickel - 009
- Matte Black - 031

## ALSO IN

- Bath
- Close-to-Ceiling

## PAIR WITH

- Calhoun
- Hemsworth

P400199-009



The versatile Durrell Collection will find a home in any coastal, modern farmhouse, or vintage setting in need of gorgeous generous illumination. Featuring a variety of versatile materials including a sailcloth linen shade and wooden accents. Durrell will showcase a lighting experience that is welcoming and sophisticated.

*Sophisticated*

*Curved Arms*

*Brushed Nickel*



P400200-009



P500210-009

# Durrell

**SEMI-FLUSH CONVERTIBLE**  
**P350150-009** Brushed Nickel  
 Hanging and ceiling mount hardware included  
 16" dia., 13-1/2" ht.,  
 Overall ht. w/chain 47", wire 10'.  
 Three candelabra base lamps, each 60w max.

**FIVE-LIGHT CHANDELIER**  
**P400199-009** Brushed Nickel  
 26-1/2" dia., 22-1/2" ht.,  
 Overall ht. w/chain 97-1/2", wire 15'.  
 Five candelabra base lamps, each 60w max.

**NINE-LIGHT CHANDELIER**  
**P400200-009** Brushed Nickel  
 32" dia., 24-1/2" ht.,  
 Overall ht. w/chain 99-1/2", wire 15'.  
 Nine candelabra base lamps, each 60w max.

**FOUR-LIGHT CHANDELIER**  
**P400218-009** Brushed Nickel  
 21" dia., 22-1/2" ht.,  
 Overall ht. w/chain 97-1/2", wire 15'.  
 Four candelabra base lamps, each 60w max.

**FOUR-LIGHT FOYER**  
**P500210-009** Brushed Nickel  
 18" dia., 28-1/2" ht.,  
 Overall ht. w/chain 103-1/2", wire 15'.  
 Four candelabra base lamps, each 60w max.

**WALL BRACKET**  
**P710074-009** Brushed Nickel  
 4-1/2" W., 12" ht.,  
 Extends 5". H/CTR 6".  
 One candelabra base lamp, 60w max.

*All fixtures shown with EF4T8D927/JA8 LED lamps, not included.*



P400199-009



P400218-009



P350150-009  
 shown hanging



P350150-009  
 shown as ceiling mount



P710074-009



P400200-031



P500210-031



P400199-031



P400218-031



P350150-031  
shown hanging



P350150-031  
shown as ceiling mount



P710074-031

# Durrell

**SEMI-FLUSH CONVERTIBLE**  
**P350150-031** Matte Black  
 Hanging and ceiling mount  
 hardware included  
 16" dia., 13-1/2" ht.,  
 Overall ht. w/chain 47", wire 10'.  
 Three candelabra base lamps,  
 each 60w max.

**FIVE-LIGHT CHANDELIER**  
**P400199-031** Matte Black  
 26-1/2" dia., 22-1/2" ht.,  
 Overall ht. w/chain 97-1/2", wire 15'.  
 Five candelabra base lamps,  
 each 60w max.

**NINE-LIGHT CHANDELIER**  
**P400200-031** Matte Black  
 32" dia., 24-1/2" ht.,  
 Overall ht. w/chain 99-1/2", wire 15'.  
 Nine candelabra base lamps,  
 each 60w max.

**FOUR-LIGHT CHANDELIER**  
**P400218-031** Matte Black  
 21" dia., 22-1/2" ht.,  
 Overall ht. w/chain 97-1/2", wire 15'.  
 Four candelabra base lamps,  
 each 60w max.

**FOUR-LIGHT FOYER**  
**P500210-031** Matte Black  
 18" dia., 28-1/2" ht.,  
 Overall ht. w/chain 103-1/2", wire 15'.  
 Four candelabra base lamps,  
 each 60w max.

**WALL BRACKET**  
**P710074-031** Matte Black  
 4-1/2" W., 12" ht.,  
 Extends 5". H/CTR 6".  
 One candelabra base lamp,  
 60w max.

*All fixtures shown with EF4T8D927/JA8 LED lamps, not included.*



# Durrell

## FINISHES

- Brushed Nickel - 009
- Matte Black - 031

## ALSO IN

- Collections
- Close-to-Ceiling

P300263-009

The versatile Durrell Collection will find a home in any coastal, modern farmhouse, or vintage electric setting in need of generous illumination. Curved arms sweep outwards from an oval backplate, clasping clear glass shades for a lighting experience that is welcoming, sophisticated and fun.

*Clear Glass Shades*



*Brushed Nickel*

*Vintage Look*

### ONE-LIGHT BATH

**P300261-009** Brushed Nickel  
4-5/8" W., 7-7/8" ht.  
Extends 6-1/4". H/CTR 4".  
One medium base lamp,  
60w max.



P300261-009

### TWO-LIGHT BATH

**P300262-009** Brushed Nickel  
13-1/2" W., 7-7/8" ht.  
Extends 6-1/4". H/CTR 5-1/4".  
Two medium base lamps,  
each 60w max.



P300264-009

### THREE-LIGHT BATH

**P300263-009** Brushed Nickel  
22-3/8" W., 7-7/8" ht.  
Extends 6-1/4". H/CTR 5-1/4".  
Three medium base lamps,  
each 60w max.



P300262-009



P300263-009

All fixtures mount up or down.

# Durrell

### ONE-LIGHT BATH

**P300261-031** Matte Black  
4-5/8" W., 7-7/8" ht.  
Extends 6-1/4". H/CTR 4".  
One medium base lamp,  
60w max.



P300261-031



P300262-031

### TWO-LIGHT BATH

**P300262-031** Matte Black  
13-1/2" W., 7-7/8" ht.  
Extends 6-1/4". H/CTR 5-1/4".  
Two medium base lamps,  
each 60w max.

### THREE-LIGHT BATH

**P300263-031** Matte Black  
22-3/8" W., 7-7/8" ht.  
Extends 6-1/4". H/CTR 5-1/4".  
Three medium base lamps,  
each 60w max.



P300263-031

### FOUR-LIGHT BATH

**P300264-031** Matte Black  
31-1/4" W., 7-7/8" ht.  
Extends 6-1/4". H/CTR 5-1/4".  
Four medium base lamps,  
each 60w max.



P300264-031

All fixtures mount up or down.  
Shown with P7825-01 vintage lamps,  
not included.

# Durrell

---

An open and airy circular metal frame surrounds simple light bases.

## **TWO-LIGHT FLUSH MOUNT**

**P350151-009** Brushed Nickel

**P350151-031** Matte Black

13" dia., 6-1/2" ht.

Two medium base lamps,  
each 60w max.



P350151-031



P350151-009

## **SEMI-FLUSH CONVERTIBLE**

**P350150-009** Brushed Nickel

**P350150-031** Matte Black

Hanging and ceiling mount  
hardware included.

16" dia., 13-1/2" ht.,

Overall ht. w/chain 47", wire 10'.

Three candelabra base lamps,  
each 60w max.



P350150-031\*



P350150-009\*

*\*Fixtures shown with P7826-01 vintage  
lamps, not included.*

# Durrell

---

Curved arms sweep outwards from a faux wood, oval backplate.

**P710074-009** Brushed Nickel

**P710074-031** Black

4-1/2" W., 12" ht.

Extends 5". H/CTR 6".

One candelabra base lamp,

60w max.

*Fixture shown with P7826-01  
vintage lamp.*

P710074-031



P710074-009

