

Foster

FINISH
● Gilded Iron - 071

ALSO IN
Close-to-Ceiling

PAIR WITH
Remix
Range

P400153-071

Clean ironwork inspired by antique trains defines the look of Foster. Substance and form are the watchwords of this family, with a simple design of bent metal arms enclosing exposed bulbs held by an ornamental socket cover. Foster's squared lines and mixed metal elements are ideal for Industrial and Rustic settings.

Bent Metal Arms

Clean Ironwork



Industrial and Rustic



Featuring Foster

Foster



P400154-071



P500155-071

FIVE-LIGHT CHANDELIER
P400153-071 Gilded Iron
25" dia., 14" ht.,
Overall ht. w/stem 80-1/2"; wire 12'.
Five medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P400154-071 Gilded Iron
30" dia., 14" ht.,
Overall ht. w/stem 81"; wire 12'.
Six medium base lamps,
each 60w max.

MINI-PENDANT
P500155-071 Gilded Iron
11-1/4" dia., 10-3/4" ht.,
Overall ht. w/stem 77"; wire 10'.
One medium base lamp,
60w max.

*All fixtures shown with
F7ST19DLED927/JA8 LED lamps,
not included.*

Foster

Iron metal arms hold light bulbs within the frame for an open, yet intimate structure.

TWO-LIGHT FLUSH MOUNT

P350116-071 Gilded Iron
16" dia., 6" ht.
Two medium base lamps,
each 60w max.

Fixture shown with P7825-01 vintage lamp, not included.



P350116-071