

Gulliver

FINISHES

- Galvanized - 141
- Graphite - 143

ALSO IN

- Bath
- Ceiling Fans
- Close-to-Ceiling
- Sconces

PAIR WITH

- Briarwood
- Conestee

P500090-143

Three circular bands wrap together to create an open design for Gulliver. Dual toned frame color combinations are hand painted Galvanized with antique white accents or Graphite with weathered gray accents. Embossed wood grained texture complements Rustic and Modern Farmhouse home décor, as well as Urban Industrial and Coastal interior settings.

Open Band Design



Hand-Painted Wood Grain

Dual Toned Frame



P400097-141

Gulliver

SEMI-FLUSH CONVERTIBLE

P350049-141 Galvanized
Hanging and ceiling mount hardware included.
17" dia., 13-1/2" ht.,
Overall ht. w/chain 52-1/2", wire 10'.
Three medium base lamps, each 75w max.

FOUR-LIGHT LINEAR CHANDELIER

P400097-141 Galvanized
38-1/2" W., 10-1/2" D., 17" ht.,
Overall ht. w/chain 91-1/2", wire 15'.
Four medium base lamps, each 75w max.

MINI-PENDANT

P500022-141 Galvanized
8-1/12" dia., 10" ht.,
Overall ht. w/chain 85", wire 10'.
One medium base lamp, 75w max.

FOUR-LIGHT PENDANT

P500023-141 Galvanized
21-5/8" dia., 18-1/4" ht.,
Overall ht. w/chain 93-1/2", wire 10'.
Four medium base lamps, each 75w max.

FIVE-LIGHT PENDANT

P500090-141 Galvanized
27-3/4" dia., 22-3/4" ht.,
Overall ht. w/chain 93-1/2", wire 10'.
Five medium base lamps, each 75w max.

WALL BRACKET

P710031-141 Galvanized
6" dia., 12" ht.,
Extends 7". H/CTR 9-3/8".
One medium base lamp, 75w max.



P500090-141



P350049-141
shown as ceiling mount



P500023-141



P500022-141



P710031-141

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



Go For A Seamless Flow

It's all about flow in an open concept home, and the number one way to achieve that is to use the same flooring throughout. Stick to a cohesive color scheme on the walls to continue the seamless look throughout the space. Next, repeat favorite elements, like the rich wood grain texture of the mantle that is seen again in the circular bands of the Gulliver linear chandelier and eccentric dining chairs which complement the elongated shape of the fixture. Finally, tie the space together by using calm, neutral tones throughout the furnishings in the living area.

Gulliver



P400097-143

SEMI-FLUSH CONVERTIBLE

P350049-143 Graphite
Hanging and ceiling mount hardware included.
17" dia., 13-1/2" ht.,
Overall ht. w/chain 52-1/2"; wire 10'.
Three medium base lamps, each 75w max.

FOUR-LIGHT LINEAR CHANDELIER

P400097-143 Graphite
38-1/2" W., 10-1/2" D., 17" ht.,
Overall ht. w/chain 91-1/2", wire 15'.
Four medium base lamps, each 75w max.



P500090-143



P350049-143

MINI-PENDANT

P500022-143 Graphite
8-1/2" dia., 10" ht.,
Overall ht. w/chain 85"; wire 10'.
One medium base lamp, 75w max.

FOUR-LIGHT PENDANT

P500023-143 Graphite
21-5/8" dia., 18-1/4" ht.,
Overall ht. w/chain 93-1/2"; wire 10'.
Four medium base lamps, each 75w max.

FIVE-LIGHT PENDANT

P500090-143 Graphite
27-3/4" dia., 22-3/4" ht.,
Overall ht. w/chain 93-1/2", wire 10'.
Five medium base lamps, each 75w max.



P500023-143



P500022-143

WALL BRACKET

P710031-143 Graphite
6" dia., 12" ht.,
Extends 7". H/CTR 9-3/8".
One medium base lamp, 75w max.



P710031-143

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Gulliver

P400158-141
shown with P860041-000 shade

Arching and delicate details curve to create an airy design in new Gulliver options. Dual-toned frame color combinations are Galvanized with antique white accents and Graphite with weathered gray accents. The hand painted wood grained texture complements Coastal and Farmhouse home décor. Accessory shades are available in Natural Burlap or Flax Linen options.

Airy Design

Accessory Shade Option



Dual Toned Frame



P500158-141



P400159-141
shown with
P860042-000
shade



P500157-141



P400158-141*



P350117-141*
shown hanging



P350117-141
shown as ceiling mount

SEMI-FLUSH CONVERTIBLE
P350117-141 Galvanized
Hanging and ceiling mount hardware included.
14-7/8" dia., 12-5/8" ht.,
Overall ht. w/chain 53"; wire 10'.
Four candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400158-141 Galvanized
26" dia., 30" ht.,
Overall ht. w/chain 105-1/2"; wire 12'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400159-141 Galvanized
35-1/4" dia., 40-1/2" ht.,
Overall ht. w/chain 163-1/2"; wire 12'.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500157-141 Galvanized
17" dia., 26-1/4" ht.,
Overall ht. w/chain 102-1/2"; wire 12'.
Four candelabra base lamps, each 60w max.

EIGHT-LIGHT FOYER
P500158-141 Galvanized
21" dia., 33-3/4" ht.,
Overall ht. w/chain 108-1/2"; wire 12'.
Eight candelabra base lamps, each 60w max.

ACCESSORY SHADE
P860041-000 Natural Burlap
1" uno-style candle fitter
6" dia., 5-1/8" ht.

ACCESSORY SHADE
P860042-000 Flax Linen
1" uno-style candle fitter
6" dia., 5-1/8" ht.

*Fixtures shown with P7826-01 vintage lamps, not included. See page 824.



P860041-000



P860042-000