

# Replay

## FINISHES

- Polished Nickel - 104
- Black - 31

## ALSO IN

Bath  
Close-to-Ceiling

## PAIR WITH

Alexa  
Tobin  
Markor

## WALL BRACKET

**P2131-104** Polished Nickel  
5" W., 9-3/4" ht.,  
Extends 5-7/8". H/CTR 7-1/4".  
One medium base lamp, 100w max.

## SEMI-FLUSH CONVERTIBLE

**P3424-104** Polished Nickel  
Hanging and ceiling mount  
hardware included.  
14-3/4" dia., 10" ht.,  
Overall ht. w/chain 50"; wire 10'.  
Two medium base lamps,  
each 100w max.

## THREE-LIGHT PENDANT

**P3450-104** Polished Nickel  
16-5/8" dia., 19" ht.,  
Overall ht. w/chain 92-1/2"; wire 15'.  
Three medium base lamps,  
each 100w max.

## THREE-LIGHT CHANDELIER

**P4318-104** Polished Nickel  
17" dia., 19-5/8" ht.,  
Overall ht. w/chain 95"; wire 15'.  
Three medium base lamps,  
each 100w max.

## FIVE-LIGHT CHANDELIER

**P4319-104** Polished Nickel  
21" dia., 19-5/8" ht.,  
Overall ht. w/chain 95"; wire 15'.  
Three medium base lamps,  
each 100w max.

## NINE-LIGHT CHANDELIER

**P4726-104** Polished Nickel  
25-1/2" dia., 28" ht.,  
Overall ht. w/chain 104"; wire 15'.  
Nine medium base lamps,  
each 100w max.

## MINI-PENDANT

**P5170-104** Polished Nickel  
4" dia., 6" ht.,  
Overall ht. w/stem 72"; wire 10'.  
One medium base lamp, 100w max.

## FOUR-LIGHT FOYER

**P500206-104** Polished Nickel  
18" dia., 31-3/4" ht.,  
Overall ht. w/chain 106"; wire 12'.  
Four medium base lamps,  
each 100w max.



# Replay

## WALL BRACKET

**P2131-31** Black  
5" W., 9-3/4" ht.,  
Extends 5-7/8". H/CTR 7-1/4".  
One medium base lamp,  
100w max.

## SEMI-FLUSH CONVERTIBLE

**P3424-31** Black  
Hanging and ceiling mount  
hardware included.  
14-3/4" dia., 10" ht.,  
Overall ht. w/chain 50"; wire 10'.  
Two medium base lamps,  
each 100w max.

## THREE-LIGHT PENDANT

**P3450-31** Black  
16-5/8" dia., 19" ht.,  
Overall ht. w/stem 92-1/2"; wire 15'.  
Three medium base lamps,  
each 100w max.

## THREE-LIGHT CHANDELIER

**P4318-31** Black  
17" dia., 19-5/8" ht.,  
Overall ht. w/stem 95"; wire 15'.  
Three medium base lamps,  
each 100w max.

## FIVE-LIGHT CHANDELIER

**P4319-31** Black  
21" dia., 19-5/8" ht.,  
Overall ht. w/chain 95"; wire 15'.  
Three medium base lamps,  
each 100w max.

## NINE-LIGHT CHANDELIER

**P4726-31** Black  
25-1/2" dia., 28" ht.,  
Overall ht. w/chain 104"; wire 15'.  
Nine medium base lamps,  
each 100w max.

## MINI-PENDANT

**P5170-31** Black  
4" dia., 6" ht.,  
Overall ht. w/stem 72"; wire 10'.  
One medium base lamp,  
100w max.

## FOUR-LIGHT FOYER

**P500206-031** Black  
18" dia., 31-3/4" ht.,  
Overall ht. w/chain 106"; wire 12'.  
Four medium base lamps,  
each 100w max.

# Replay

## FINISH

● Brushed Nickel - 09

## WALL BRACKET

**P2131-09** Brushed Nickel  
5" W., 9-3/4" ht.,  
Extends 5-7/8". H/CTR 7-1/4".  
One medium base lamp,  
100w max.

## SEMI-FLUSH CONVERTIBLE

**P3424-09** Brushed Nickel  
Hanging and ceiling mount  
hardware included.  
14-3/4" dia., 10" ht.,  
Overall ht. w/chain 49-1/2", wire 10'.  
Two medium base lamps,  
each 100w max.

## THREE-LIGHT PENDANT

**P3450-09** Brushed Nickel  
16-5/8" dia., 19" ht.,  
Overall ht. w/chain 92-1/2", wire 15'.  
Three medium base lamps,  
each 100w max.

## THREE-LIGHT CHANDELIER

**P4318-09** Brushed Nickel  
17" dia., 20-1/8" ht.,  
Overall ht. w/chain 95", wire 15'.  
Three medium base lamps,  
each 100w max.

## FIVE-LIGHT CHANDELIER

**P4319-09** Brushed Nickel  
21" dia., 19-5/8" ht.,  
Overall ht. w/chain 95", wire 15'.  
Five medium base lamps,  
each 100w max.

## NINE-LIGHT CHANDELIER

**P4726-09** Brushed Nickel  
25-1/2" dia., 28" ht.,  
Overall ht. w/chain 104", wire 15'.  
Nine medium base lamps,  
each 100w max.

## MINI-PENDANT

**P5170-09** Brushed Nickel  
4" dia., 6" ht.,  
Overall Ht. W/Stem 72", wire 10'.  
One medium base lamp,  
100w max.

## FOUR-LIGHT FOYER

**P500206-009** Brushed Nickel  
18" dia., 31-3/4" ht.,  
Overall ht. w/chain 106"; wire 12'.  
Four medium base lamps,  
each 100w max.



P3424-09  
shown as  
ceiling mount



P4319-09  
shown with glass  
facing up



P5170-09



P2131-09



P4726-09



P500206-009



P4318-09  
shown with glass  
facing down



P4663-09



P5114-09

P3030-09



P4663-20



P5114-20

P3030-20



P3954-09



P4659-20



P3954-20



P4659-20

# Orbitz

## FINISH

● Brushed Nickel - 09  
● Antique Bronze - 20

## ALSO IN

Bath

## PAIR WITH

Topsail

Tally

Equinox

## WALL BRACKET

**P3030-09** Brushed Nickel  
**P3030-20** Antique Bronze  
5-1/2" W., 7-1/4" ht.,  
Extends 6". H/CTR 5".  
One medium base lamp,  
100w max.

## THREE-LIGHT CHANDELIER

**P3954-09** Brushed Nickel  
**P3954-20** Antique Bronze  
Hanging and ceiling mount  
hardware included.  
17" dia., 12 1/4" ht.,  
Overall ht. w/stem 79"; wire 15'.  
Three medium base lamps,  
each 100w max.

## FIVE-LIGHT CHANDELIER

**P4659-09** Brushed Nickel  
**P4659-20** Antique Bronze  
23-1/4" dia., 18-1/2" ht.,  
Overall ht. w/chain 85"; wire 15'.  
Five medium base lamps,  
each 100w max.

## NINE-LIGHT CHANDELIER

**P4663-09** Brushed Nickel  
**P4663-20** Antique Bronze  
27" dia., 23-3/4" ht.,  
Overall ht. w/stem 90"; wire 15'.  
Nine medium base lamps,  
each 100w max.

## MINI-PENDANT

**P5114-09** Brushed Nickel  
**P5114-20** Antique Bronze  
4" dia., 7-3/4" ht.,  
Overall ht. w/chain or stem 78"; wire 10'.  
One medium base lamp,  
100w max.

# Replay

---

Etched glass, linear details and a pleasingly elegant frame.



P3424-09



P3424-104



P3424-31

## TWO-LIGHT FLUSH MOUNT

**P3423-09** Brushed Nickel

**P3423-31** Black

**P3423-104** Polished Nickel  
14" dia., 5-3/4" ht.

Two medium base lamps,  
each 100w max.



P3423-09



P3423-104



P3423-31

## SEMI-FLUSH CONVERTIBLE

**P3424-09** Brushed Nickel

**P3424-31** Black

**P3424-104** Polished Nickel  
Hanging and ceiling mount  
hardware included.  
14-3/4" dia., 10" ht.

Overall ht. w/chain 50"; wire 10'

Two medium base lamps,  
each 100w max.

# Replay

Highlighted by simple forms, linear details and etched opal glass. A pleasingly elegant frame enhances a simplified modern look within the Replay collection.

## FINISHES

- Brushed Nickel - 09
- Black - 31

## ALSO IN

Collections  
Close-to-Ceiling

## ONE-LIGHT BATH

**P2131-09** Brushed Nickel

**P2131-31** Black

5-1/8" W., 9-3/4" ht.

Extends 5-7/8". H/CTR 7-1/4".

One medium base lamp,  
100w max.

## TWO-LIGHT BATH

**P2158-09** Brushed Nickel

**P2158-31** Black

13" W., 7-7/8" ht.

Extends 6". H/CTR 5-1/4".

Two medium base lamps,  
each 100w max.

## THREE-LIGHT BATH

**P2159-09** Brushed Nickel

**P2159-31** Black

22" W., 7-7/8" ht.

Extends 6". H/CTR 5-1/4".

Three medium base lamps,  
each 100w max.

## FOUR-LIGHT BATH

**P2160-09** Brushed Nickel

**P2160-31** Black

31-1/8" W., 7-7/8" ht.

Extends 6". H/CTR 5-1/4".

Four medium base lamps,  
each 100w max.

*All fixtures mount up or down.*



P2131-09



P2158-09



P2159-09



P2160-09



P2131-31



P2158-31



P2159-31



P2160-31

Featuring Replay



# Replay

## FINISHES

- Antique Bronze - 20
- Polished Nickel - 104

## ALSO IN

Collections  
Close-to-Ceiling

## ONE-LIGHT BATH

**P2131-20** Antique Bronze

**P2131-104** Polished Nickel

5-1/8" W., 9-3/4" ht.

Extends 5-7/8". H/CTR 7-1/4".

One medium base lamp,  
100w max.



P2131-104



P2158-104

## TWO-LIGHT BATH

**P2159-20** Antique Bronze

**P2159-104** Polished Nickel

13" W., 7-7/8" ht.

Extends 6". H/CTR 5-1/4".

Two medium base lamps,  
each 100w max.



P2159-104

## THREE-LIGHT BATH

**P2159-20** Antique Bronze

**P2159-104** Polished Nickel

22" W., 7-7/8" ht.

Extends 6". H/CTR 5-1/4".

Three medium base lamps,  
each 100w max.



P2160-104

## FOUR-LIGHT BATH

**P2160-20** Antique Bronze

**P2160-104** Polished Nickel

31-1/8" W., 7-7/8" ht.

Extends 6". H/CTR 5-1/4".

Four medium base lamps,  
each 100w max.



P2131-20



P2158-20

*All fixtures mount up or down.*



P2159-20



P2160-20