

Alexa

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Haven
Kempsey
Mast

WALL BRACKET

P2959-09 Brushed Nickel
One-light. Mounts up or down.
4-1/2" W., 9-3/8" ht.,
Extends 6-1/8".
One medium base lamp, 100w max.

THREE-LIGHT PENDANT

P3846-09 Brushed Nickel
18" dia., 24-3/8" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT FOYER

P3977-09 Brushed Nickel
18" W., 44-3/8" ht.,
Overall ht. w/chain 119"; wire 15'.
Four medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER

P4458-09 Brushed Nickel
17" dia., 19-5/8" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4459-09 Brushed Nickel
20" dia., 19-3/4" ht.,
Overall ht. w/chain 95"; wire 15'.
Five medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P4619-09 Brushed Nickel
34" W., 4-1/2" D., 20" ht.,
Overall ht. w/chain 93"; wire 15'.
Four medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4626-09 Brushed Nickel
28" dia., 28-1/2" ht.,
Overall ht. w/chain 102"; wire 15'.
Nine medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P4758-09 Brushed Nickel
25" dia., 19-3/4" ht.,
Overall ht. w/chain 95"; wire 15'.
Six medium base lamps,
each 100w max.

MINI-PENDANT

P5147-09 Brushed Nickel
5-1/8" dia., 7-3/4" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp, 100w max.



P3977-09



P4626-09



P4626-20



P3977-20



P4458-09



P4758-09



P4758-20



P4458-20



P4459-09



P5147-09



P3846-09



P3846-20



P5147-20



P4459-20



P4619-09



P2959-09



P2959-20



P4619-20

Alexa

WALL BRACKET

P2959-20 Antique Bronze
One-light. Mounts up or down.
4-1/2" W., 9-3/8" ht.,
Extends 6-1/8".
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P3846-20 Antique Bronze
18" dia., 24-3/8" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT FOYER

P3977-20 Antique Bronze
18" W., 44-3/8" ht.,
Overall ht. w/chain 119"; wire 15'.
Four medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER

P4458-20 Antique Bronze
17" dia., 19-5/8" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4459-20 Antique Bronze
20" dia., 19-3/4" ht.,
Overall ht. w/chain 95"; wire 15'.
Five medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P4619-20 Antique Bronze
34" W., 4-1/2" D., 20" ht.,
Overall ht. w/chain 93"; wire 15'.
Four medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4626-20 Antique Bronze
28" dia., 28-1/2" ht.,
Overall ht. w/chain 102"; wire 15'.
Nine medium base lamps,
each 100w max.

SIX-LIGHT CHANDELIER

P4758-20 Antique Bronze
25" dia., 19-3/4" ht.,
Overall ht. w/chain 95"; wire 15'.
Six medium base lamps,
each 100w max.

MINI-PENDANT

P5147-20 Antique Bronze
5-1/8" dia., 7-3/4" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp,
100w max.

Alexa

Featuring a transitional design style, this collection offers the best of traditional and modern details. Etched linen and clear glass with Brushed Nickel finish. Umber etched linen and clear glass with Antique Bronze finish.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2959-09 Brushed Nickel
P2959-20 Antique Bronze
4-1/2" W., 9-3/8" ht.
Extends 6-1/8". H/CTR 5-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2977-09 Brushed Nickel
P2977-20 Antique Bronze
13" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2978-09 Brushed Nickel
P2978-20 Antique Bronze
22" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2998-09 Brushed Nickel
P2998-20 Antique Bronze
31" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2959-09



P2977-09



P2978-09



P2998-09



P2959-20



P2977-20



P2978-20



P2998-20

Alexa

Etched linen finished glass is complemented with a crisp, clear edge accent strip.

TWO-LIGHT SEMI-FLUSH

P2851-09 Brushed Nickel

P2851-20 Antique Bronze

12-1/4" dia., 11" ht.

Two medium base lamps, each 100w max.



P2851-09



P2851-20

TWO-LIGHT FLUSH MOUNT

P3620-09 Brushed Nickel

P3620-20 Antique Bronze

12-1/4" dia., 6-3/8" ht.

Two medium base lamps, each 60w max.



P3620-09



P3620-20