

# Gather

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

- Bath
- Ceiling Fan

PAIR WITH

- 5-Light
- Drum Shade

SEMI-FLUSH CONVERTIBLE

**P3748-09** Brushed Nickel  
Hanging and ceiling mount hardware included.  
12-1/2" dia., 10-3/8" ht.,  
Overall ht. w/chain 24"; wire 6'.  
Two medium base lamps,  
each 100w max.

TWO-LIGHT PENDANT

**P3914-09** Brushed Nickel  
15" dia., 20-5/8" ht.,  
Overall ht. w/chain 66"; wire 8'.  
Two medium base lamps,  
each 100w max.

THREE-LIGHT CHANDELIER

**P4440-09** Brushed Nickel  
18 1/2" dia., 15" ht.,  
Overall ht. w/chain 60"; wire 8'.  
Three medium base lamps,  
each 100w max.

FIVE-LIGHT CHANDELIER

**P4441-09** Brushed Nickel  
20-1/2" dia., 15" ht.,  
Overall ht. w/chain 60"; wire 8'.  
Five medium base lamps,  
each 100w max.

NINE-LIGHT CHANDELIER

**P4627-09** Brushed Nickel  
27-3/4" dia., 20-1/2" ht.,  
Overall ht. w/chain 84"; wire 10'.  
Nine medium base lamps,  
each 100w max.

THREE-LIGHT CHANDELIER

**P4734-09** Brushed Nickel  
19-1/2" dia., 16-1/2" ht.,  
Overall ht. w/chain 61"; wire 8'.  
Three medium base lamps,  
each 100w max.

FIVE-LIGHT CHANDELIER

**P4735-09** Brushed Nickel  
23" dia., 17-1/2" ht.,  
Overall ht. w/chain 62"; wire 8'.  
Five medium base lamps,  
each 100w max.

MINI-PENDANT

**P5113-09** Brushed Nickel  
4" dia., 5-3/4" ht., Overall ht.  
w/chain or stem 63"; wire 8'.  
One medium base lamp, 100w max.



P4440-09



P4627-09



P4627-20



P4440-20



P4734-09



P4735-09



P4735-20



P4734-20



P3914-09



P4441-09



P4441-20



P3914-20



P3748-09  
*shown hanging*



P5113-09



P5113-20



P3748-20  
*shown hanging*

# Gather

SEMI-FLUSH CONVERTIBLE

**P3748-20** Antique Bronze  
Hanging and ceiling mount hardware included.  
12-1/2" dia., 10-3/8" ht.,  
Overall ht. w/chain 24"; wire 6'.  
Two medium base lamps,  
each 100w max.

TWO-LIGHT PENDANT

**P3914-20** Antique Bronze  
15" dia., 20-5/8" ht.,  
Overall ht. w/chain 66"; wire 8'.  
Two medium base lamps,  
each 100w max.

THREE-LIGHT CHANDELIER

**P4440-20** Antique Bronze  
18 1/2" dia., 15" ht.,  
Overall ht. w/chain 60"; wire 8'.  
Three medium base lamps,  
each 100w max.

FIVE-LIGHT CHANDELIER

**P4441-20** Antique Bronze  
20-1/2" dia., 15" ht.,  
Overall ht. w/chain 60"; wire 8'.  
Five medium base lamps,  
each 100w max.

NINE-LIGHT CHANDELIER

**P4627-20** Antique Bronze  
27-3/4" dia., 20-1/2" ht.,  
Overall ht. w/chain 84"; wire 10'.  
Nine medium base lamps,  
each 100w max.

THREE-LIGHT CHANDELIER

**P4734-20** Antique Bronze  
19-1/2" dia., 16-1/2" ht.,  
Overall ht. w/chain 61"; wire 8'.  
Three medium base lamps,  
each 100w max.

FIVE-LIGHT CHANDELIER

**P4735-20** Antique Bronze  
23" dia., 17-1/2" ht.,  
Overall ht. w/chain 62"; wire 8'.  
Five medium base lamps,  
each 100w max.

MINI-PENDANT

**P5113-20** Antique Bronze  
4" dia., 5-3/4" ht., Overall ht.  
w/chain or stem 63"; wire 8'.  
One medium base lamp,  
100w max.

# Gather

## FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

## THREE-LIGHT FOYER

**P3928-09** Brushed Nickel

**P3928-20** Antique Bronze

10" dia., 16" ht.,  
Overall ht. w/chain 61"; wire 8'.  
Three candelabra base lamps,  
each 60w max.

## SIX-LIGHT FOYER

**P3929-09** Brushed Nickel

**P3929-20** Antique Bronze

15" dia., 24" ht.,  
Overall ht. w/chain 87"; wire 10'.  
Six candelabra base lamps,  
each 60w max.

## WALL BRACKET

**P2706-09** Brushed Nickel

**P2706-20** Antique Bronze

5" W., 7-1/2" ht.,  
Extends 6-1/2". H/CTR 2-5/8".  
One medium base lamp,  
100w max.



P3929-09  
shown with included  
Brushed Nickel  
candle sleeves



P3929-20  
shown with included  
White candle sleeves



P3928-09  
shown with included  
White candle sleeves



P3928-20  
shown with included  
Antique Bronze  
candle sleeves



P2706-09



P2706-20

# Gather

Simplified frame with updated styling and elegant etched glass shades.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections

ONE-LIGHT BATH

**P2706-09** Brushed Nickel  
**P2706-15** Polished Chrome  
**P2706-20** Antique Bronze  
5" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-5/8".  
One medium base lamp, 100w max.

TWO-LIGHT BATH

**P2707-09** Brushed Nickel  
**P2707-15** Polished Chrome  
**P2707-20** Antique Bronze  
12" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-1/2".  
Two medium base lamps, each 100w max.

THREE-LIGHT BATH

**P2708-09** Brushed Nickel  
**P2708-15** Polished Chrome  
**P2708-20** Antique Bronze  
24" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-1/2".  
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

**P2709-09** Brushed Nickel  
**P2709-15** Polished Chrome  
**P2709-20** Antique Bronze  
30" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-1/2".  
Four medium base lamps, each 100w max.

All fixtures mount up or down.



P2706-09



P2709-09



P2707-09



P2708-09



P2706-15



P2709-15



P2707-15



P2708-15



P2706-20



P2709-20



P2707-20



P2708-20



P2713-09



P2714-09



P2713-15



P2714-15



P2713-20



P2714-20

# Gather

FIVE-LIGHT BATH

**P2713-09** Brushed Nickel  
**P2713-15** Polished Chrome  
**P2713-20** Antique Bronze  
36" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-1/2".  
Five medium base lamps, each 100w max.

SIX-LIGHT BATH

**P2714-09** Brushed Nickel  
**P2714-15** Polished Chrome  
**P2714-20** Antique Bronze  
48" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-1/2".  
Six medium base lamps, each 100w max.

All fixtures mount up or down.

# Gather LED

Sleek frame features updated styling and elegant etched glass shades.

## SEMI-FLUSH CONVERTIBLE

**P350088-009-30** Brushed Nickel

**P350088-015-30** Polished Chrome

**P350088-020-30** Antique Bronze

Hanging and ceiling mount hardware included.

12-7/8" dia., 10-3/8" ht.,

Overall ht. w/chain 50", wire 10'.

One 17w LED module, 3000K, 90CRI, 1276 source lumens.

All fixtures:



P350088-020-30  
shown as hanging



P350088-009-30  
shown as hanging



P350088-015-30  
shown as hanging



P350088-015-30

# Gather

---

Sleek frame features updated styling and elegant etched glass shades.

**SEMI-FLUSH CONVERTIBLE**

**P3748-09** Brushed Nickel

**P3748-20** Antique Bronze

Hanging and ceiling mount hardware included.

13" dia., 10-3/8" ht.

Overall ht. w/chain 24"; wire 6'.

Two medium base lamps, each 100w max.



P3748-09



P3748-20