

# Invite

## FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

## ALSO IN

Bath  
Close-to-Ceiling

## PAIR WITH

Gather  
Riley

## WALL BRACKET

**P2041-09** Brushed Nickel  
6-1/2" W., 11-1/2" ht.,  
Extends 8-1/4". H/CTR 3-3/4".  
One medium base lamp, 100w max.

## SEMI-FLUSH CONVERTIBLE

**P3694-09** Brushed Nickel  
Hanging and ceiling mount  
hardware included.  
15" dia., 5-1/4" ht.,  
Overall ht. w/stem 71"; wire 12'.  
Three medium base lamps,  
each 100w max.

## THREE-LIGHT CHANDELIER

**P4695-09** Brushed Nickel  
22" dia., 19-3/4" ht.,  
Overall ht. w/stem 86"; wire 12'.  
Three medium base lamps,  
each 100w max.

## FIVE-LIGHT CHANDELIER

**P4696-09** Brushed Nickel  
25-1/4" dia., 20-3/4" ht.,  
Overall ht. w/stem 87"; wire 12'.  
Five medium base lamps,  
each 100w max.

## NINE-LIGHT CHANDELIER

**P4697-09** Brushed Nickel  
35-5/8" dia., 26-1/2" ht.,  
Overall ht. w/stem 92"; wire 12'.  
Nine medium base lamps,  
each 100w max.

## TWELVE-LIGHT CHANDELIER

**P4725-09** Brushed Nickel  
49" dia., 38" ht.,  
Overall ht. w/chain 161"; wire 15'.  
Twelve medium base lamps,  
each 75w max.

## FOUR-LIGHT PENDANT

**P5047-09** Brushed Nickel  
20" dia., 27-3/8" ht.,  
Overall ht. w/stem 93"; wire 12'.  
Four medium base lamps,  
each 100w max.

## MINI-PENDANT

**P5110-09** Brushed Nickel  
6-1/2" dia., 7-3/8" ht.,  
Overall ht. w/stem 74"; wire 10'.  
One medium base lamp, 100w max.



# Invite

## WALL BRACKET

**P2041-20** Antique Bronze  
6-1/2" W., 11-1/2" ht.,  
Extends 8-1/4". H/CTR 3-3/4".  
One medium base lamp, 100w max.

## SEMI-FLUSH CONVERTIBLE

**P3694-20** Antique Bronze  
Hanging and ceiling mount  
hardware included.  
15" dia., 5-1/4" ht.,  
Overall ht. w/stem 71"; wire 12'.  
Three medium base lamps,  
each 100w max.

## THREE-LIGHT CHANDELIER

**P4695-20** Antique Bronze  
22" dia., 19-3/4" ht.,  
Overall ht. w/stem 86"; wire 12'.  
Three medium base lamps,  
each 100w max.

## FIVE-LIGHT CHANDELIER

**P4696-20** Antique Bronze  
25-1/4" dia., 20-3/4" ht.,  
Overall ht. w/stem 87"; wire 12'.  
Five medium base lamps,  
each 100w max.

## NINE-LIGHT CHANDELIER

**P4697-20** Antique Bronze  
35-5/8" dia., 26-1/2" ht.,  
Overall ht. w/stem 92"; wire 15'.  
Nine medium base lamps,  
each 100w max.

## TWELVE-LIGHT CHANDELIER

**P4725-20** Antique Bronze  
49" dia., 38" ht.,  
Overall ht. w/chain 161"; wire 12'.  
Twelve medium base lamps,  
each 75w max.

## FOUR-LIGHT PENDANT

**P5047-20** Antique Bronze  
20" dia., 27-3/8" ht.,  
Overall ht. w/stem 93"; wire 12'.  
Four medium base lamps,  
each 100w max.

## MINI-PENDANT

**P5110-20** Antique Bronze  
6-1/2" dia., 7-3/8" ht.,  
Overall ht. w/stem 74"; wire 10'.  
One medium base lamp, 100w max.

# Invite

Dual-layer etched glass and mylar drum shades on a linear frame offer a modern style.

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

## ALSO IN

Collections  
Close-to-Ceiling

## ONE-LIGHT BATH

**P2041-20** Antique Bronze  
**P2041-09** Brushed Nickel  
6-1/2" W., 11-1/2" ht.  
Extends 8-1/4". H/CTR 3-3/4".  
One medium base lamp,  
100w max.

## TWO-LIGHT BATH

**P2078-20** Antique Bronze  
**P2078-09** Brushed Nickel  
14-1/2" W., 7-3/8" ht.  
Extends 7-1/2". H/CTR 4-7/8".  
Two medium base lamps,  
each 100w max.

## THREE-LIGHT BATH

**P2079-20** Antique Bronze  
**P2079-09** Brushed Nickel  
23-1/2" W., 7-3/8" ht.  
Extends 7-1/2". H/CTR 4-7/8".  
Three medium base lamps,  
each 100w max.

## FOUR-LIGHT BATH

**P2080-20** Antique Bronze  
**P2080-09** Brushed Nickel  
32-1/2" W., 7-3/8" ht.  
Extends 7-1/2". H/CTR 4-7/8".  
Four medium base lamps,  
each 100w max.

## FIVE-LIGHT BATH

**P2081-20** Antique Bronze  
**P2081-09** Brushed Nickel  
41-1/2" W., 7-3/8" ht.  
Extends 7-1/2". H/CTR 4-7/8".  
Five medium base lamps,  
each 100w max.



P2080-09



P2041-09



P2078-09



P2079-09



P2081-09



P2080-20



P2041-20



P2078-20



P2079-20



P2081-20

# Invite

---

Etched glass with translucent mylar drum shade.

## TWO-LIGHT FLUSH MOUNT

**P3693-09** Brushed Nickel

**P3693-20** Antique Bronze

12" dia., 5-3/8" ht.

Two medium base lamps, each 60w max.



P3694-09



P3694-20

## SEMI-FLUSH CONVERTIBLE

**P3694-09** Brushed Nickel

**P3694-20** Antique Bronze

Hanging and ceiling mount hardware included.

15" dia., 5-1/4" ht.,

Overall ht. w/stem 71"; wire 12'.

Three medium base lamps, each 100w max.



P3693-09



P3693-20