

Farris

P250002-108-30
shown with Walnut blades

FINISHES

- Brushed Nickel - 009
- Oil Rubbed Bronze - 108
- Graphite - 143

Farris features three solid wood carved blades to form a sleek, modern design. The 60" ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.



Modern Design

Wood Carved Blades

Removable LED Light



P250002-009-30
shown with Gray Weathered Wood blades



P250002-108-30
shown with Walnut blades
and light kit removed



P250002-143-30
shown with Driftwood blades

Farris

P250002-009-30 Brushed Nickel



Gray Weathered Wood

P250002-108-30 Oil Rubbed Bronze



Walnut

P250002-143-30 Graphite



Driftwood

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,047 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	223 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit
- White opal shatterproof shade
- Full function remote control with batteries is included

SIZE

60" dia., 15-1/2" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.

