

Gulliver

FINISHES

- Galvanized - 141
- Graphite - 143

P250012-141-22
shown with Antique White Wood



Urban Industrial Design

Rustic Charm

Hand-Painted Wood

Three circular bands wrap together to create an open design for . Fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.



P250012-141-22
shown with Antique White Wood



P250012-143-22
shown with Gray Wood

Gulliver

P250012-141-22 Galvanized



Antique White Wood

P250012-143-22 Galvanized



Gray Wood

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,297 cubic feet per minute
Electricity Use	39 watts (excludes lights)
Airflow Efficiency	33 cubic feet per minute per watt



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5")
- AC Motor
- Reversible Motor
- Remote control with batteries is included
- Rust-proof non-metallic blades

SIZE

23" dia., 18-1/8" ht.
80" lead wires.

LAMP

Three LED medium base vintage lamps, 2200K, 80 CRI, 5.5w max each, included, dimmable.

