

# Loring

## FINISHES

- Black- 031
- Galvanized - 141

P250006-031  
shown with Matte Black blades

Outfitted with stylish mixed metal elements, the Loring Collection shows off an industrial-inspired, open-cage design. Four plywood blades and a handy remote control are ready to help you and your family stay comfortable and relaxed all year round.

*Open-Cage Design*



*Industrial Inspired*

*Mixed-Metal Elements*



P250006-031  
shown with Gold accent  
and Distressed Ebony blades



P250006-141  
shown with Matte Black accent  
and White Barnwood blades

## Loring

### P250006-031 Black

- Matte Black
- Distressed Ebony

### P250006-141 Galvanized

- White Barnwood
- Driftwood

#### ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	1,766 cubic feet per minute
<b>Electricity Use</b>	43 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	44 CFM/W

#### FEATURES

- Limited lifetime warranty
- Close-to-ceiling installation
- AC Motor
- Reversible plywood blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

#### SIZE

33" dia., 15-1/4" ht.  
80" lead wires.



Three Speed Remote Control Included  
*Three-speed fan operation*