

# Prismatic

A bold and striking prismatic glass shade is the focal point in these pendants. Featuring a sleek Brushed Nickel cap and stems highlighting the industrial styling.

## FINISH

● Brushed Nickel - 09

## PENDANT

**P5182-09** Brushed Nickel  
12-5/8" dia., 11" ht.  
Overall ht. w/stem 53"; wire 10'.  
One medium base lamp,  
100w max.

## PENDANT

**P5183-09** Brushed Nickel  
16" dia., 13-1/2" ht.  
Overall ht. w/stem 56"; wire 10'.  
One medium base lamp,  
150w max.

## LED PENDANT

**P5143-0930K9** Brushed Nickel  
12-3/4" dia., 10-7/8" ht.  
Overall ht. w/stem 77"; wire 10'.  
One 9w LED module 3000K, 90CRI  
623 source lumens.



P5183-09



P5182-09



P5143-0930K9

