

Glass Domes

Classically styled with an etched glass dome shade, solid trim, and decorative knobs.

ONE-LIGHT FLUSH MOUNT

P350043-009 Brushed Nickel

P350043-143 Graphite

11" dia., 5-3/8" ht.

One medium base lamp,
60w max.



P350043-009



P350043-143

TWO-LIGHT FLUSH MOUNT

P350044-009 Brushed Nickel

P350044-143 Graphite

14" dia., 6-1/2" ht.

Two medium base lamps,
each 75w max.



P350044-009



P350044-143

THREE-LIGHT FLUSH MOUNT

P350045-009 Brushed Nickel

P350045-143 Graphite

16-1/2" dia., 6-3/8" ht.

Three medium base lamps,
each 60w max.



P350045-009



P350045-143

SEMI-FLUSH CONVERTIBLE

P350133-009 Brushed Nickel

P350133-143 Graphite

Hanging and ceiling mount
hardware included.

15" dia., 11" ht.

Three medium base lamps,
each 75w max.



P350133-009



P350133-143