

# Bezel LED

Sleek and slim in appearance with etched white glass shade offering a pleasant glow from the bottom and sides.

## LED FLUSH MOUNT

**P350085-009-30** Brushed Nickel  
**P350085-015-30** Polished Chrome  
**P350085-020-30** Antique Bronze  
10-1/2" dia., 3-1/2" ht.  
One 17w LED module, 3000K, 90CRI, 1276 source lumens.



P350085-009-30



P350085-020-30



P350085-015-30

## LED FLUSH MOUNT

**P350086-009-30** Brushed Nickel  
**P350086-015-30** Polished Chrome  
**P350086-020-30** Antique Bronze  
13" dia., 3-7/8" ht.  
One 25w LED module, 3000K, 90CRI, 1770 source lumens.



P350086-020-30



P350086-015-30

## LED FLUSH MOUNT

**P350087-009-30** Brushed Nickel  
**P350087-015-30** Polished Chrome  
**P350087-020-30** Antique Bronze  
16" dia., 4-3/4" ht.  
One 26w LED module, 3000K, 90CRI, 1770 source lumens.

All fixtures:



P350086-009-30



P350087-009-30



P350087-020-30



P350087-015-30