

FINISHES

- Black - 031
- Stainless Steel - 135

ALSO IN

Close-to-Ceiling

P300265-135

Incorporate a vintage feel with a dash of industrial personality with the Dwyer Collection. Attention-grabbing, clear, ribbed glass takes center stage in this design, creating a gaslight glow when the fixture is illuminated. Simple metal frames encase the glass panes to emphasize the collection's chic industrial edge.

Industrial Design



Ribbed Glass Panes

Gaslight Glow

TWO-LIGHT BATH

P300265-135 Stainless Steel
14" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Two G16.5 candelabra base lamps,
each 60w max.



P300265-135

THREE-LIGHT BATH

P300266-135 Stainless Steel
22" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Three G16.5 candelabra base lamps,
each 60w max.



P300266-135

FOUR-LIGHT BATH

P300267-135 Stainless Steel
30" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Four G16.5 candelabra base lamps,
each 60w max.



P300267-135

TWO-LIGHT BATH

P300265-031 Black
14" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Two G16.5 candelabra base lamps,
each 60w max.



P300265-031

THREE-LIGHT BATH

P300266-031 Black
22" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Three G16.5 candelabra base lamps,
each 60w max.



P300266-031

FOUR-LIGHT BATH

P300267-031 Black
30" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Four G16.5 candelabra base lamps,
each 60w max.



P300267-031

Dwyer

Clear ribbed glass framed by simple metal banding creates a gaslight glow.

TWO-LIGHT FLUSH MOUNT

P350152-031 Black

P350152-135 Stainless Steel

11" sq., 4" ht.

Two medium base lamps,
each 60w max.



P350152-031



P350152-135