

# Signal

## FINISHES

- Polished Chrome - 015
- Graphite - 143

## ALSO IN

Close-to-Ceiling

P300175-015

Signal has an industrial origin, yet its clean lines beckon a modern sensibility. Clear blown glass shades deliver a lighter touch, balancing the substantial look of the metal angular arm and round backplate. With its emphasis on simplicity and function, Signal is ideal for many residential settings.

*Modern  
Sensibility*



*Clean Glass*

*Round Backplate*

### ONE-LIGHT BATH

**P300174-015** Polished Chrome  
5-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
One medium base lamp,  
60w max.



P300174-015

P300175-015

### TWO-LIGHT BATH

**P300175-015** Polished Chrome  
13-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Two medium base lamps,  
each 60w max.

### THREE-LIGHT BATH

**P300176-015** Polished Chrome  
23-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Three medium base lamps,  
each 60w max.

### FOUR-LIGHT BATH

**P300177-015** Polished Chrome  
33-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Four medium base lamps,  
each 60w max.



P300175-015

P300176-015

*All fixtures mount up or down.*

# Signal

### ONE-LIGHT BATH

**P300174-143** Graphite  
5-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
One medium base lamp,  
60w max.



P300174-143

P300175-143

### TWO-LIGHT BATH

**P300175-143** Graphite  
13-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Two medium base lamps,  
each 60w max.



P300176-143

### THREE-LIGHT BATH

**P300176-143** Graphite  
23-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Three medium base lamps,  
each 60w max.

### FOUR-LIGHT BATH

**P300177-143** Graphite  
33-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Four medium base lamps,  
each 60w max.

*All fixtures mount up or down.*

# Signal

---

Clear blown glass shade and a clean-lined frame offers a modern attitude.

**ONE-LIGHT FLUSH MOUNT**

**P350145-015** Polished Chrome

**P350145-143** Graphite

5-1/8" dia., 7-5/8" ht.

One medium base lamp,

60w max.



P350145-143



P350145-015