

Miter LED

FINISH

● Brushed Nickel - 009

P300152-009-30

The Miter LED wall sconce highlights a beautiful layered effect to enhance a variety of interior areas. Each clear beveled glass panel is hand cut and positioned together, creating visual interest that extend to the corners. To complete the form, a backplate and linear accents frame the glass in a Brushed Nickel finish. An integrated LED source provides a variety of energy and cost savings benefits.

Clear Beveled Glass

Hand Cut



Linear Accents

24" LINEAR LED BATH

P300152-009-30 Brushed Nickel

24" W., 5" ht.

Extends 3-7/8". H/CTR 2-1/2".

36w integrated LED, 3000K, 90CRI, 1975 delivered lumens.

34" LINEAR LED BATH

P300153-009-30 Brushed Nickel

34-1/8" W., 5" ht.

Extends 3-7/8". H/CTR 2-1/2".

53w integrated LED, 3000K, 90CRI, 2825 delivered lumens.

12" LED WALL BRACKET

P710061-009-30 Brushed Nickel

5" W., 12-1/4" ht.

Extends 3-7/8". H/CTR 6-1/8".

16w integrated LED, 3000K, 90CRI, 825 delivered lumens.



P710061-009-30



P300152-009-30



P300152-009-30
mounted vertical



P300153-009-30

All fixtures can be installed horizontally or vertically.

All fixtures:

