

Phase 1.2 LED

FINISH

● Brushed Nickel - 009

P300205-009-30
shown with decorative
geometric diffuser

A classic form with contemporary updates, this elongated acrylic shade comes with decorative accents. Both a faux stone option and white geometric decorative diffuser are included to further customize the fixture. An integrated LED source provides uniform illumination, as well as energy and cost savings benefits.

Classic Form



Decorative Accents

Acrylic Shade



P300223-009-30
mounted vertical



P300205-009-30
shown with faux stone diffuser



P300206-009-30
shown with decorative geometric diffuser



P300207-009-30
shown with faux stone diffuser

24" LINEAR LED BATH

P300205-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
22w integrated LED, 3000K,
90CRI, 1575 delivered lumens.

36" LINEAR LED BATH


P300206-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
33w integrated LED, 3000K,
90CRI, 2475 delivered lumens.

48" LINEAR LED BATH


P300207-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
42w integrated LED, 3000K,
90CRI, 3400 delivered lumens.

All fixtures can be installed
horizontally or vertically.

All fixtures:



Detail of faux
stone accent



Detail of
geometric accent