

LED TRACK

Ideal for residential and light commercial applications, this LED Track Kit is provided with all components required for installation. Track Kits include 42" of linear track, a floating power feed, three AC LED Track Heads and installation hardware. Track Heads feature a frosted glass lens to reduce glare.

LED FEATURES

- 120v input voltage.
- 2700K color temperature; 90+ CRI.
- Flicker free dimming down to 10% with many Triac forward or reverse ELV phase dimmers.
- 50,000 hr. life.

Track Kits

P900002-028-27 Satin White

P900002-031-27 Black

42" L., 2-7/8" W., 6-1/2" ht.,
Extends 2-3/4".

Three 9.5W LED,
2700K, 1575 lumens.

P900003-028-27 Satin White

P900003-031-27 Black

42" L., 3-1/4" W., 7-1/2" ht.,
Extends 3-1/4".

Three 14.5W LED,
2700K, 2350 lumens.

All fixtures:



AC LED Track Heads

P900000 and P900001 Track Heads are compatible with P900002 and P900003 Track Kits.

These AC LED Track Heads can be added to a track kit to provide more light when needed.

P900000-028-27 Satin White

P900000-031-27 Black

2-7/8" W., 6-1/2" ht.,
Extends 2-3/4".

One 9.5W LED,
2700K, 533 lumens.

P900001-028-27 Satin White

P900001-031-27 Black

3-1/4" W., 7-1/2" ht.,
Extends 3-1/4".

One 14.5W LED,
2700K, 797 lumens.



P900000-028-27



P900000-031-27



P900001-028-27



P900001-031-27

All fixtures:

