

Decorative Surface Mount

Get the perfect lighting for any situation or task with our Decorative Surface Mount Triac Dimming Collection. This collection offers a flicker-free dimming lighting solution that allows the fixture to dim down to 10% with many Triac or forward phase dimmers. Choose from two different sizes of round surface mounts, each in a beautiful brushed nickel finish and trimmed with etched glass for an added level of aesthetic appeal. Wet location listed.

P8147-09-30K Brushed Nickel

Round trim with etched glass
7-1/4" dia., 2-3/4" ht.

10.5w integrated LED, 3000K, 90CRI,
690 lumens, 66 lumens per watt.



P8147-09-30K
Triac/ELV dimming

P8247-09-30K Brushed Nickel

Round with etched glass
5-1/2" dia., 1-1/2" ht.

10.5w integrated LED, 3000K, 90CRI,
690 lumens, 66 lumens per watt.



P8247-09-30K
Triac/ELV dimming

All fixtures:

