

Intrinsic Surface Mount LED

Elevate your design vision with just the flip of a switch with our Intrinsic Surface Mount LED Collection. The simple, classic design of these light fixtures can easily be installed into a variety of style applications in both residential and commercial settings. We offer two different sizes of surface mounts, both coated in a crisp white finish, to meet your unique design needs. Each smooth trim ring surrounds an integrated LED light fixture ready to emit general ambient lighting wherever it calls home in your design plan.

P810012-028-30 White
5-1/2" dia., 1" ht.
12w integrated LED,
3000K, 90CRI, 600 lumens.



P810012-028-30

P810013-028-30 White
7-1/2" dia., 1-3/16" ht.
15.5w integrated LED,
3000K, 90CRI, 1000 lumens.



P810013-028-30K

All fixtures:



LED FEATURES

- Wet location listed.
- 120v input voltage.
- 60 Lumens per watt.
- Flicker-free dimming with many Triac and ELV dimmers.
- 50,000 hour life.