

Directionals & Track

Ideal Adjustable Light.

Round Back Directionals

THREE-LIGHT

P6160-09 Brushed Nickel

P6160-30 White

P6160-174 Urban Bronze

Wall or ceiling mount round back.

27" W., 5-1/4" ht.

Extends 6-5/8". H/CTR 2-3/8".

Three PAR20 lamps, each 50w max.



P6160-09



P6160-30



P6160-174



P6162-09



P6162-174

FOUR-LIGHT

P6162-09 Brushed Nickel

P6162-174 Urban Bronze

Wall or ceiling mount round back.

36" W., 5-1/8" ht.

Extends 6-5/8".

Four PAR20 lamps, each 50w max.

On-Off Switch Round Back Directionals

ONE-LIGHT

P6155-09 Brushed Nickel

P6155-30 White

Wall mount round back.

On/off switch.

3-3/4" dia., 5" ht.

Extends 6-7/8".

One PAR20 medium base lamp,

50w max.



P6155-30



P6155-09

Round Back Directionals

ONE-LIGHT

P6147-09 Brushed Nickel

P6147-30 White

P6147-174 Urban Bronze

Ceiling mount round back.

5" dia., 3-3/4" ht.

Extends 6-1/2".

One PAR20 medium base lamp,

50w max.



P6147-09



P6149-09

TWO-LIGHT

P6149-09 Brushed Nickel

P6149-30 White

P6149-174 Urban Bronze

Wall or ceiling mount round back.

9" dia., 3-3/4" ht.

Extends 6-1/2".

Two PAR20 medium base lamps, each

50w max.



P6147-30



P6149-30



P6144-30

ONE-LIGHT

P6144-30 White

P6144-174 Urban Bronze

Wall or ceiling mount round back.

5" dia., 5-1/2" ht.

Extends 7".

One PAR30 medium base lamp,

75w max.



P6147-174



P6149-174



P6144-174

Heat Lamp Flat Back Directionals

ONE LIGHT

P6397-30 White

Adjustable wall or ceiling heat lamp with black baffle.

5-3/4" dia., 8-1/8" ht.

Extends 11".

One BR-40 medium base lamp,

250w max.



P6397-30