

# Burlington



P6537-20



P6615-20



P550035-020



P6616-20



P6437-20



P6617-20

The Burlington collection features all aluminum construction, weather-resistant performance with clear beveled glass panels.

## FINISH

● Antique Bronze - 20

## POST LANTERN

**P6437-20** Antique Bronze  
9" sq., 18-3/8" ht.  
Fits 3" post (sold separately).  
Two candelabra base lamps,  
each 60w max.

## HANGING LANTERN

**P6537-20** Antique Bronze  
9" sq., 15-3/4" ht.  
Overall ht. w/chain 91"; wire 10'.  
Two candelabra base lamps,  
each 60w max.

## FLUSH MOUNT

**P550035-020** Antique Bronze  
7" sq., 7" ht.  
One medium base lamp,  
each 60w max.

## SMALL WALL LANTERN

**P6615-20** Antique Bronze  
7" W., 12-7/8" ht.  
Extends 7-3/4". H/CTR 4-1/8".  
One medium base lamp,  
100w max.

## MEDIUM WALL LANTERN

**P6616-20** Antique Bronze  
9" W., 18-3/4" ht.  
Extends 9-3/4". H/CTR 7-5/8".  
Two candelabra base lamps,  
each 60w max.

## LARGE WALL LANTERN

**P6617-20** Antique Bronze  
11" W., 21-7/8" ht.  
Extends 11-3/4". H/CTR 8-5/8".  
Three candelabra base lamps,  
each 60w max.