

# Bulkheads LED

Robust and energy efficient, LED bulkheads are a general-purpose luminaire. Comprised of a die-cast aluminum frame and polycarbonate diffuser. Fixtures are impact resistant and offer various mounting options and can be widely adopted for indoor and outdoor applications.

## OVAL WALL OR CEILING

**P3647-3030K9** White

**P3647-3130K9** Black

6-1/2" W., 10-1/2" ht.

Extends 4-3/8". H/CTR 5-1/4".

One 9w LED module, 3000K, 90CRI, 623 source lumens.

## ROUND WALL OR CEILING

**P3648-3030K9** White

**P3648-3130K9** Black

9-1/2" dia., 4-3/8" ht.

H/CTR 4-3/4".

One 17w LED module, 3000K, 90CRI, 623 source lumens.

## OVAL WALL OR CEILING

**P3649-3030K9** White

**P3649-3130K9** Black

6-1/2" W., 10-1/2" ht.

Extends 4-1/2". H/CTR 5-1/4".

One 9w LED module, 3000K, 90CRI, 623 source lumens.

## ROUND WALL OR CEILING

**P3650-3030K9** White

**P3650-3130K9** Black

9-1/2" dia., 4-1/2" ht.

H/CTR 4-3/4".

One 9w LED module, 3000K, 90CRI, 623 source lumens.

All fixtures:



P3647-3030K9  
*shown wall-mounted*



P3647-3130K9  
*shown ceiling-mounted*



P3649-3130K9  
*shown wall-mounted*



P3649-3030K9  
*shown ceiling-mounted*



P3648-3130K9  
*shown wall-mounted*



P3648-3030K9  
*shown ceiling-mounted*



P3650-3130K9  
*shown wall-mounted*



P3650-3030K9  
*shown ceiling-mounted*

# Bulkheads

---

Die-cast aluminum with clear glass lens.

## OVAL WALL OR CEILING

**P3706-30** White

**P3706-31** Black

6-3/8" W., 11" ht.

Extends 5". H/CTR 5-1/2".

One medium base lamp,  
100w max.



P3706-31  
*shown ceiling-mounted*



P3709-30  
*shown wall-mounted*

## ROUND WALL OR CEILING

**P3709-30** White

**P3709-31** Black

7-7/8" dia., 4-1/2" ht.

H/CTR 4".

One medium base lamp,  
60w max.



P3709-31  
*shown ceiling-mounted*



P3706-30  
*shown wall-mounted*