

Aluminum Cylinders LED

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. Listed for wet locations.

3" Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P563000-020-30K	Antique Bronze	One-light down	5-1/2" W., 5-5/8" ht.	1 12w integrated LED,
P563000-030-30K	White	For wet locations		3000K, 90CRI,
P563000-143-30K	Graphite			900 delivered lumens
P563000-147-30K	Satin Nickel			
P563001-020-30K	Antique Bronze	Two-light up/down	5-1/2" W., 8-1/4" ht.	2 24w integrated LED,
P563001-030-30K	White	For wet locations		3000K, 90CRI,
P563001-143-30K	Graphite			1800 delivered lumens
P563001-147-30K	Satin Nickel			

All fixtures:



P563000-020-30K



P563000-030-30K



P563000-143-30K



P563000-147-30K



P563001-020-30K



P563001-030-30K



P563001-143-30K



P563001-147-30K



P5674-20/30K



P5674-30/30K



P5674-31/30K



P5674-82/30K



P5675-20/30K



P5675-30/30K



P5675-31/30K



P5675-82/30K



P5774-20/30K



P5774-30/30K



P5774-31/30K



P5774-82/30K

Aluminum Cylinders LED

5" Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5674-20/30K	Bronze	One-light down.	5" W., 7-1/4" ht.	1 17w integrated LED
P5674-30/30K	White		Extends 8".	3000K, 90CRI,
P5674-31/30K	Black		H/CTR 2-1/2".	531 delivered lumens
P5674-82/30K	Metallic Gray			
P5675-20/30K	Bronze	Two-light up/down	5" W., 14" ht.	2 17w integrated LED,
P5675-30/30K	White	For wet locations	Extends 8".	3000K, 90CRI,
P5675-31/30K	Black	requires top cover	H/CTR 7".	1025 delivered lumens
P5675-82/30K	Metallic Gray	lens, P860045.		
P5774-20/30K	Bronze	One-light. Mounts	5" dia., 6-1/2" ht.	1 17w integrated LED,
P5774-30/30K	White	flush to ceiling.		3000K, 90CRI,
P5774-31/30K	Black			764 delivered lumens
P5774-82/30K	Metallic Gray			

All fixtures:

