

# Spades

## FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Graphite - 143

P2570-15  
shown with Black blades

The 56" Spades ceiling fan features a sleek contemporary two-blade design that is finished in Brushed Nickel, Polished Chrome or Graphite options. Spades features a dual mount system, an energy saving DC motor and ABS composite blades. A full function remote control is included.

*Dual Mount System*

*Contemporary Design*

*Sleek Blades*

# Spades

**P2570-09** Brushed Nickel

 Silver

**P2570-15** Polished Chrome

 Black

**P2570-143** Graphite

 Graphite



P2570-09  
shown with Silver blades



P2570-15  
shown with Black blades



P2570-143  
shown with Graphite blades

## ENERGY INFORMATION AT HIGH SPEED

<b>Airflow</b>	6,746 cubic feet per minute
<b>Electricity Use</b>	32 watts (excludes lights)
<b>DOE Weighted CFM/W</b>	215 CFM/W



Full Function Remote Control Included  
Six-speed fan operation  
Reverse direction control

## FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17°)
- Close-to-ceiling installation
- DC Motor
- Non-reversible ABS blades
- Remote control with batteries is included

## SIZE

56" dia., 18-1/8" ht  
80" lead wires.



## CTC INSTALLATION

