

Teasley

Featuring coastal influences and farmhouse charm, the Teasley 56" 5-blade ceiling fan is suitable for a variety of interior settings. Clear seeded bell-shaped glass shades highlight Architectural Bronze, Graphite or Galvanized finish options. Three vintage LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.

FINISHES

- Architectural Bronze - 129
- Galvanized - 141
- Graphite - 143

P250004-129 Architectural Bronze



Distressed Walnut
American Walnut

P250004-141 Galvanized



Driftwood
Gray Weathered Wood

P250004-143 Graphite



American Walnut
Gray Weathered Wood



P250004-129
shown with Brushed Bronze accents
and American Walnut blades



P250004-141
shown with Brushed Nickel accents
and Gray Weathered Wood blades



P250004-143
shown with Brushed Nickel accents
and Gray Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,749 cubic feet per minute
Electricity Use	76 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Clear seeded glass shades
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

56" dia., 22-1/2" ht.
80" lead wires.

LAMP

Three medium base vintage lamps, each 7w max included, dimmable.

