


Glandon

Glandon offers a sophisticated design that is ideal for settings requiring a touch of modern flair. Six reversible blades in a Walnut/Driftwood faux wood finish are strapped by a sleek Antique Nickel metal bar for an unexpected industrial detail. The 60" Glandon ceiling fan features a 17w LED module (3000K color temperature) with a shatterproof white opal shade finish and a dual mount system. Full range dimming and remote control is included.


FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2586-7130K Gilded Iron



P2586-8130K Antique Nickel



P2586-7130K
shown with Toasted Oak blades



P2586-8130K
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,036 cubic feet per minute
Electricity Use	84 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass
- Remote control with batteries is included

SIZE

60" dia., 17-1/8" ht
80" lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.



Remote Control Included
Three-speed fan operation
Full-range dimming for light

