

Kudos

This five-blade 52" Kudos ceiling fan features a clear Fresnel glass shade. Available in a Brushed Nickel, Polished Chrome or Antique Bronze finish and includes a remote control. The Kudos features a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.




P2568-0930K
shown with American Walnut blades


FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20


P2568-0930K Brushed Nickel



P2568-1530K Polished Chrome



P2568-2030K Antique Bronze



P2568-1530K
shown with Black blades



P2568-2030K
shown with Cherry blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,160 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood Blades
- Clear Fresnel glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

52" dia., 17-5/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.

