

Albin

The Albin Collection offers a modern take on a traditional design that will be perfectly at home in so many outdoor spaces and lifestyles. Five blades finished with a faux wood grain texture extend from a modern-style center available in an architectural bronze, matte white, or matte black finish. An LED light source is encased in a crisp shade to illuminate a patio or porch space that will beg to be lived in an enjoyed.

FINISHES

- Satin White- 028
- Black- 031
- Architectural Bronze - 129


P250036-028-30 Satin White



P250036-031-30 Black



P250036-129-30 Architectural Bronze



P250036-028-30
shown with Satin White blades



P250036-031-30
shown with Toasted Oak blades



P250036-129-30
shown with Distressed Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,740 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	95 CFM/W



Three Speed Remote Control Included
Three speed fan operation
Full range dimming with light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White Opal glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15-5/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI,
2000 lumens, dimmable.

