

Decorative Patio Fan



P2526-20
shown with Washed Walnut blades

FINISH

● Antique Bronze - 20

P2526-20 Antique Bronze



Washed Walnut



P2526-20
shown with P2636-20WB light kit*
and Washed Walnut blades
* Light kit sold separately.

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,150 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	77 CFM/W

FEATURES

- 15-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Damp location listed

SIZE

52" dia., 17-3/8" ht.
CTC 12-3/16 ht.
80" lead wires.



CTC INSTALLATION

