

Indoor/Outdoor

Universal-style with quick-connect wiring.

SCHOOLHOUSE

P2601-20WB Antique Bronze

P2601-30WB White

P2601-80WB Forged Black

P2601-141WB Galvanized
with opal glass.

8-1/2" dia., 7" ht.

One medium base, 3000K,
LED lamp included.

800 lumens/lamp, 90 CRI.
(dimnable)



P2601-20WB



P2601-30WB



P2601-80WB



P2601-141WB



LOW PROFILE

P2611-20WB Antique Bronze

P2611-30WB White

P2611-80WB Forged Black

with opal glass.

10-1/2" dia., 4-1/2" ht.

Two medium base, 3000K,
LED lamp included.

800 lumens/lamp, 90 CRI.
(dimnable)



P2611-20WB



P2611-30WB



P2611-80WB



ASHMORE

P2636-20WB Antique Bronze
with frosted seeded glass.

11" dia., 8-1/4" ht.

Two medium base, 3000K,
LED lamp included.

800 lumens/lamp, 90 CRI.
(dimnable)



P2636-20WB

