

Braden



P2588-0930K
shown with American Walnut blades



P2588-1530K
shown with Black blades



P2588-12930K
shown with Medium Cherry blades

This Braden 56", three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A shatterproof white opal glass shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits. Featuring a larger motor, Braden moves more air than a traditional hugger ceiling fan.


FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Architectural Bronze - 129


P2588-0930K Brushed Nickel



P2588-1530K Polished Chrome



P2588-12930K Architectural Bronze



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,263 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

56" dia., 9-7/8" ht.
12" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

