

CAPTARENT

80+ CRI

MTO

Product No.	Finish	Size	Source	Input	Dimming
PCIM1-2543-830-U	Mirrored	24-3/4" W., 43" ht., Extends 2-3/8". ADA	25W Integrated LED, 1140 nominal lumens	120 - 277V	0-10V
PCIM1-2543-835-U					
PCIM1-2543-840-U					
PCIM1-3143-830-U		31-3/4" W., 43" ht., Extends 2-3/8". ADA	36W Integrated LED, 1650 nominal lumens		
PCIM1-3143-835-U					
PCIM1-3143-840-U					
PCIM1-3743-830-U		37-3/4" W., 43" ht., Extends 2-3/8". ADA	36W Integrated LED, 1690 nominal lumens		
PCIM1-3743-835-U					
PCIM1-3743-840-U					

LED FEATURES

- Architecturally designed to provide soft, pleasing illumination
- Perimeter etched panels are indirectly backlit to provide uniform illumination
- Available in three sizes: 25"x43", 31"x43" and 37"x43"
- 80+ or 90+ CRI; Available in 3000K, 3500K, and 4000K color temperature options
- Universal (120-277) voltage, 0-10V dimming capable
- Mirror edges have brushed, radius treatment for consistency in appearance
- Easy installation of metal housing; simple, hanging attachment of mirror to housing.

90+ CRI

MTO

Product No.	Finish	Size	Source	Input	Dimming		
PCIM1-2543-930-U	Mirrored	24-3/4" W., 43" ht., Extends 2-3/8". ADA	25W Integrated LED, 1140 nominal lumens	120 - 277V	0-10V		
PCIM1-3143-930-U						31-3/4" W., 43" ht., Extends 2-3/8". ADA	36W Integrated LED, 1650 nominal lumens
PCIM1-3743-930-U							



PCIM1-3143-840-U