

HANSFORD



P400147-020



Hansford features a clear, spherical shade paired with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the elegant nickel finish to bring tranquility to your home with Hansford's classic style. Featuring a clean and precise design with generous scale. Hansford lends itself to Farmhouse, Coastal or Industrial interiors. Available in Polished Nickel or Antique Bronze finishes.

- FINISH**
- Antique Bronze - 020
 - Polished Nickel - 104

ALSO AVAILABLE IN
Bath & Vanity at
progresslighting.com



P400146-020



P400146-104

THREE-LIGHT CHANDELIER
P400146-020 Antique Bronze
P400146-104 Polished Nickel
 21" dia., 16-7/8" ht.
 Overall ht. w/stem 85", wire 180".
 Three medium base lamps,
 each 100w max.

FIVE-LIGHT CHANDELIER
P400147-020 Antique Bronze
P400147-104 Polished Nickel
 25" dia., 19-1/8" ht.
 Overall ht. w/stem 87", wire 180".
 Five medium base lamps,
 each 100w max.

*Fixtures shown with
 F8.5A19DLED927/JA8 LED lamps.*



P400146-020
 installed as
 semi-flush



P400147-104



P400147-020

HANSFORD



Hansford features a clear, spherical shade with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the gleaming nickel finish to bring tranquility to your home with Hansford's classic style. Installs up or down.

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

ALSO AVAILABLE IN

Close-to-Ceiling

ONE-LIGHT BATH

P300049-020 Antique Bronze

P300049-104 Polished Nickel

6-1/2" W., 9-1/2" ht.

Extends 7-1/4". H/CTR 6-7/8".

One medium base lamp, 100w max.

TWO-LIGHT BATH

P300050-020 Antique Bronze

P300050-104 Polished Nickel

15-1/2" W., 10-7/8" ht.

Extends 7-1/4". H/CTR 8-1/4".

Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P300051-020 Antique Bronze

P300051-104 Polished Nickel

24-1/2" W., 10-7/8" ht.

Extends 7-1/4". H/CTR 8-1/4".

Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P300052-020 Antique Bronze

P300052-104 Polished Nickel

33-1/2" W., 10-7/8" ht.

Extends 7-1/4". H/CTR 8-1/4".

Four medium base lamps, each 100w max.

Shown with P7825-01 vintage lamps



P300049-020



P300049-104



P300050-020
Installed up



P300050-104



P300051-020



P300051-104



P300052-020



P300052-104
Installed up

HANSFORD

Hansford features a clear, spherical shade paired with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the gleaming nickel finish to bring tranquility to your home with Hansford's classic style.

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

ALSO AVAILABLE IN

Bath & Vanity, page 76

ONE-LIGHT FLUSH MOUNT

P350046-020 Antique Bronze

P350046-104 Polished Nickel

10" dia., 12-5/8" ht.

One medium base lamp,
100w max.

*Shown with P7825-01
vintage lamp*

P350046-020



P350046-104

