

SANTIAGO



P4587-80

Casual details meet rustic design. Featuring spiraled detailing, scrolled arms, romantic jasmine mist glass, subtle forged iron twists, and Forged Black finish.

FINISH
● Forged Black - 80

ALSO AVAILABLE IN
Bath & Vanity
Close-to-Ceiling

PAIR WITH
Enclave
Greyson



P4179-80

WALL BRACKET
P2752-80 Forged Black
6-3/8" W., 11" ht.
Extends 7", H/CTR 7-7/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3839-80 Forged Black
Hanging and ceiling mount
hardware included.
20-1/4" dia., 14-1/2" ht.
Overall ht. w/chain 91"; wire 15'.
Three medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER
P4179-80 Forged Black
Two-tier.
32" dia., 29-1/4" ht.
Overall ht. w/chain 104"; wire 15'.
Nine candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P4587-80 Forged Black
With one-light downlight
(can be turned on/off with
integral column switch).
24-1/4" dia., 23" ht.
Overall ht. w/chain 98"; wire 15'.
Five candelabra base lamps,
each 60w max. and one 50w max.
R-20 lamp in downlight.



P3839-80



P2752-80



Shown: P4588-80 chandelier (Image: Toll Brothers)

SANTIAGO



P4588-80

WALL BRACKET
P2753-80 Forged Black
 14" W., 11" ht.
 Extends 7". H/CTR 7-7/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT FOYER
P3840-80 Forged Black
 14-1/4" dia., 27-3/4" ht.
 Overall ht. w/chain 103"; wire 15'.
 Three candelabra base lamps,
 each 60w max.

THREE-LIGHT CHANDELIER
P4586-80 Forged Black
 18" dia., 18-5/8" ht.
 Overall ht. w/chain 92"; wire 15'.
 Three candelabra base lamps,
 each 60w max.

SIX-LIGHT OVAL CHANDELIER
P4588-80 Forged Black
 37-7/8" L., 26" W.
 Overall ht. w/chain 99"; wire 15'.
 Six candelabra base lamps,
 each 60w max.

MINI-PENDANT
P5076-80 Forged Black
 6-1/4" w., 15-1/4" ht.
 Overall ht. w/stem 73"; wire 10'.
 One medium base lamp,
 100w max.



P4586-80



P3840-80



P5076-80



P2753-80

SANTIAGO



P2754-80

The Santiago collection offers spiraled detailing and subtle twists. Forged Black finish with Jasmine mist glass.

FINISH

- Forged Black - 80

ALSO AVAILABLE IN

Fixture Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2752-80 Forged Black
6-3/8" W., 11" ht.
Extends 7". H/CTR 7-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2753-80 Forged Black
14" W., 11" ht.
Extends 7". H/CTR 7-7/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2754-80 Forged Black
21" W., 11" ht.
Extends 7". H/CTR 7-7/8".
Three medium base lamps,
each 100w max.



P2752-80



P2753-80



P2754-80

SANTIAGO

Jasmine mist glass with subtle forged iron twists and iron frame.



P3839-80



P3837-80

TWO-LIGHT FLUSH MOUNT

P3837-80 Forged Black
14-3/8" dia., 8-1/8" ht.
Two medium base lamps,
each 75w max.

SEMI-FLUSH CONVERTIBLE

P3839-80 Forged Black
Hanging and ceiling mount
hardware included.
19-7/8" dia., 14-1/4" ht.
Three medium base lamps,
each 75w max.