

SPIRIT



P4605-144



The spirit of craftsmanship prevails with subtle forms. Light amber etched glass shades. Pebbles finish offers a galvanized metal look or Antique Bronze finish for a classic style.

FINISHES

- Antique Bronze - 20
- Pebbles - 144

ALSO AVAILABLE IN

- Bath & Vanity
- Close-to-Ceiling



P4611-144

P3455-144

P4559-144

P7184-144

P4558-144

P5160-144

THREE-LIGHT INVERTED PENDANT

P3455-144 Pebbles
18" dia., 24-3/4" ht.
Overall ht. w/stem 91"; wire 15'.
Three medium base lamps, each 100w max.

TWO-LIGHT LINEAR CHANDELIER

P4558-144 Pebbles
36" L., 13-1/8" W., 23-5/8" ht.
Overall ht. w/stem 90"; wire 15'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4559-144 Pebbles
26-1/2" dia., 18-3/8" ht.
Overall ht. w/stem 84"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4605-144 Pebbles
25-1/2" dia., 25-1/8" ht.
Overall ht. w/stem 91"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P4611-144 Pebbles
Two-tier.
32-1/4" dia., 35" ht.
Overall ht. w/stem 101"; wire 15'.
Nine medium base lamps, each 100w

MINI-PENDANT

P5160-144 Pebbles
7-1/8" dia., 6-3/4" ht.
Overall ht. w/stem 73"; wire 10'.
One medium base lamp, 100w max.

WALL SCONCE

P7184-144 Pebbles
9-1/2" W., 6-3/4" ht.
Extends 4-3/4". H/CTR 2-7/8".
One medium base lamp, 100w max.



P4605-20



P4611-20

P3455-20

P4559-20

P7184-20

P4558-20

P5160-20

SPIRIT

THREE-LIGHT INVERTED PENDANT

P3455-20 Antique Bronze
18" dia., 24-3/4" ht.
Overall ht. w/stem 91"; wire 15'.
Three medium base lamps,
each 100w max.

TWO-LIGHT LINEAR CHANDELIER

P4558-20 Antique Bronze
36" L., 13-1/8" W., 23-5/8" ht.
Overall ht. w/stem 90"; wire 15'.
Two medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4559-20 Antique Bronze
26-1/2" dia., 18-3/8" ht.
Overall ht. w/stem 84"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4605-20 Antique Bronze
25-1/2" dia., 25-1/8" ht.
Overall ht. w/stem 91"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4611-20 Antique Bronze
Two-tier.
32-1/4" dia., 35" ht.
Overall ht. w/stem 101"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P5160-20 Antique Bronze
7-1/8" dia., 6-3/4" ht.
Overall ht. w/stem 73"; wire 10'.
One medium base lamp,
100w max.

WALL SCONCE

P7184-20 Antique Bronze
9-1/2" W., 6-3/4" ht.
Extends 4-3/4". H/CTR 2-7/8".
One medium base lamp,
100w max.

SPIRIT



P2135-20



P2136-20



P2137-20



P2138-20



P2135-144



P2136-144



P2137-144



P2138-144



The spirit of craftsmanship prevails with subtle forms. Light amber etched glass shades. Pebbles or Antique Bronze finish.

FINISHES

- Antique Bronze - 20
- Pebbles - 144

ALSO AVAILABLE IN

Fixture Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2135-20 Antique Bronze

P2135-144 Pebbles

7-1/8" W., 10" ht.

Extends 8-5/8". H/CTR 5".

One medium base lamp,
100w max.

TWO-LIGHT BATH

P2136-20 Antique Bronze

P2136-144 Pebbles

17" W., 7-3/4" ht.

Extends 8-1/4". H/CTR 5-1/4".

Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2137-20 Antique Bronze

P2137-144 Pebbles

27-1/2" W., 7-3/4" ht.

Extends 8-1/4". H/CTR 5-1/4".

Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2138-20 Antique Bronze

P2138-144 Pebbles

37-3/4" W., 7-3/4" ht.

Extends 8-1/4". H/CTR 5-1/4".

Four medium base lamps,
each 100w max.

SPIRIT

Light amber etched glass shades.



P3414-20



P3414-144

TWO-LIGHT SEMI-FLUSH

P3414-20 Antique Bronze

P3414-144 Pebbles

13-1/8" dia., 12-1/4" ht.

Two medium base lamps,
each 100w max.



P3500-20



P3500-144

ONE-LIGHT

P3500-20 Antique Bronze

P3500-144 Pebbles

10-3/4" dia., 5" ht.

Two medium base lamps,
each 60w max.



P3501-20



P3501-144

TWO-LIGHT

P3501-20 Antique Bronze

P3501-144 Pebbles

12-3/4" dia., 5-1/4" ht.

Two medium base lamps,
each 60w max.



P3502-20



P3502-144

THREE-LIGHT

P3502-20 Antique Bronze

P3502-144 Pebbles

14-5/8" dia., 6" ht.

Three medium base lamps,
each 60w max.