

# ALEXA



P4459-20

Traditional and modern styles come together in the Alexa collection. The Alexa family offers a fresh twist to contemporary industrial styling. Etched amber linen finished glass - complemented with a crisp, clear edge accent strip - adds a warm feel to this modern fixture family.

#### FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

#### ALSO AVAILABLE IN

Bath & Vanity  
Close-to-Ceiling

#### PAIR WITH

Equinox  
Collins  
Mingle



P3846-20



P3977-20



P4458-20



P5147-20



P4758-20



P2959-20



P4626-20



P4619-20

#### WALL BRACKET

**P2959-20** Antique Bronze  
One-light. Mounts up or down.  
4-1/2" W., 9-3/8" ht.  
Extends 6-1/8".  
One medium base lamp,  
100w max.

#### THREE-LIGHT INVERTED PENDANT

**P3846-20** Antique Bronze  
18" dia., 24-3/8" ht.  
Overall ht. w/chain 99"; wire 15'.  
Three medium base lamps,  
each 100w max.

#### FOUR-LIGHT FOYER

**P3977-20** Antique Bronze  
18" W., 44-3/8" ht.  
Overall ht. w/chain 119"; wire 15'.  
Four medium base lamps,  
each 75w max.

#### THREE-LIGHT CHANDELIER

**P458-20** Antique Bronze  
17" dia., 19-5/8" ht.  
Overall ht. w/chain 95"; wire 15'.  
Three medium base lamps,  
each 100w max.

#### FIVE-LIGHT CHANDELIER

**P4459-20** Antique Bronze  
20" dia., 19-3/4" ht.  
Overall ht. w/chain 95"; wire 15'.  
Five medium base lamps,  
each 100w max.

#### FOUR-LIGHT LINEAR CHANDELIER

**P4619-20** Antique Bronze  
34" L., 4-1/2" W., 20" ht.  
Overall ht. w/chain 93"; wire 15'.  
Four medium base lamps,  
each 100w max.

#### NINE-LIGHT CHANDELIER

**P4626-20** Antique Bronze  
Two-tier.  
28" dia., 28-1/2" ht.  
Overall ht. w/chain 102"; wire 15'.  
Nine medium base lamps,  
each 100w max.

#### SIX-LIGHT CHANDELIER

**P4758-20** Antique Bronze  
25" dia., 19-3/4" ht.  
Overall ht. w/chain 95"; wire 15'.  
Six medium base lamps,  
each 100w max.

#### MINI-PENDANT

**P5147-20** Antique Bronze  
5-1/8" dia., 7-3/4" ht.  
Overall ht. w/stem 64"; wire 10'.  
One medium base lamp,  
100w max.





Shown: P4626-09 chandelier  
(Image: Masterpiece Design Group, Studio KW)



P4458-09



P5147-09



P4459-09



P4758-09



P3846-09



P3977-09



P4626-09



P4619-09



P2959-09

# ALEXA

## WALL BRACKET

**P2959-09** Brushed Nickel  
One-light. Mounts up or down.  
4-1/2" W., 9-3/8" ht.  
Extends 6-1/8".  
One medium base lamp,  
100w max.

## THREE-LIGHT INVERTED PENDANT

**P3846-09** Brushed Nickel  
18" dia., 24-3/8" ht.  
Overall ht. w/chain 99"; wire 15'.  
Three medium base lamps,  
each 100w max.

## FOUR-LIGHT FOYER

**P3977-09** Brushed Nickel  
18" W., 44-3/8" ht.  
Overall ht. w/chain 119"; wire 15'.  
Four medium base lamps,  
each 75w max.

## THREE-LIGHT CHANDELIER

**P4458-09** Brushed Nickel  
17" dia., 19-5/8" ht.  
Overall ht. w/chain 95"; wire 15'.  
Three medium base lamps,  
each 100w max.

## FIVE-LIGHT CHANDELIER

**P4459-09** Brushed Nickel  
20" dia., 19-3/4" ht.  
Overall ht. w/chain 95"; wire 15'.  
Five medium base lamps,  
each 100w max.

## FOUR-LIGHT LINEAR CHANDELIER

**P4619-09** Brushed Nickel  
34" L., 4-1/2" W., 20" ht.  
Overall ht. w/chain 93"; wire 15'.  
Four medium base lamps,  
each 100w max.

## NINE-LIGHT CHANDELIER

**P4626-09** Brushed Nickel  
Two-tier.  
28" dia., 28-1/2" ht.  
Overall ht. w/chain 102"; wire 15'.  
Nine medium base lamps,  
each 60w max.

## SIX-LIGHT CHANDELIER

**P4758-09** Brushed Nickel  
25" dia., 19-3/4" ht.  
Overall ht. w/chain 95"; wire 15'.  
Six medium base lamps,  
each 100w max.

## MINI-PENDANT

**P5147-09** Brushed Nickel  
5-1/8" dia., 7-3/4" ht.  
Overall ht. w/stem 64"; wire 10'.  
One medium base lamp,  
100w max.



# ALEXA

Featuring a transitional design style, this collection offers the best of traditional and modern details. Etched linen and clear glass with Brushed Nickel finish. Umber etched linen and clear glass with Antique Bronze finish.

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

## ALSO AVAILABLE IN

Fixture Collections  
Close-to-Ceiling

## ONE-LIGHT BATH

**P2959-09** Brushed Nickel  
**P2959-20** Antique Bronze  
4-1/2" W., 9-3/8" ht.  
Extends 6-1/8". H/CTR 5-7/8".  
One medium base lamp,  
100w max.

## TWO-LIGHT BATH

**P2977-09** Brushed Nickel  
**P2977-20** Antique Bronze  
13" W., 9-1/2" ht.  
Extends 6-1/8". H/CTR 7-1/4".  
Two medium base lamps,  
each 100w max.

## THREE-LIGHT BATH

**P2978-09** Brushed Nickel  
**P2978-20** Antique Bronze  
22" W., 9-1/2" ht.  
Extends 6-1/8". H/CTR 7-1/4".  
Three medium base lamps,  
each 100w max.

## FOUR-LIGHT BATH

**P2998-09** Brushed Nickel  
**P2998-20** Antique Bronze  
31" W., 9-1/2" ht.  
Extends 6-1/8". H/CTR 7-1/4".  
Four medium base lamps,  
each 100w max.



P2959-20

P2977-20



P2978-20



P2998-20



P2959-09

P2977-09



P2978-09



P2998-09



Shown: P2977-09 bath fixtures

# ALEXA

---

Etched linen glass with a top clear edge accent strip with the Brushed Nickel finish and etched umber linen glass with a clear top edge accent strip with the Antique Bronze finish.

## SEMI-FLUSH CONVERTIBLE

**P2851-09** Brushed Nickel

**P2851-20** Antique Bronze

Hanging and ceiling mount hardware included.

12-1/4" dia., 11" ht.

Two medium base lamps, each 100w max.



P2851-20



P2851-09

## TWO-LIGHT FLUSH MOUNT

**P3620-09** Brushed Nickel

**P3620-20** Antique Bronze

12-1/4" dia., 6-3/8" ht.

Two medium base lamps, each 60w max.



P3620-20



P3620-09